


REVISIONS			
REV		APPR	DATE

NOTES: UNLESS OTHERWISE SPECIFIED.

1. ARTWORK P/N DEMO CIRCUIT 1322A Rev1
2. FAB PER IPC-A-600. 4-Layers.
3. MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4
.062 +/- .005 INCH THICKNESS WITH 2 OZ.
COPPER FINISH INTERNAL LAYERS AND
1 OZ. COPPER ON INTERNAL LAYERS.
FLAMMABILITY RATING: 94 V-2 MINIMUM .
4. SIZE: CUT TO DIMENSIONS AND TOLERANCES SHOWN.
0.00 ARE PRIMARY DATUMS.
5. BOARD: SELECTIVE PLATED BOARD. SOLDER
MASK OVER BARE COPPER, COLOR, GREEN LPI.
GOLD IMMERSION BOTH SIDES.
SILKSCREEN COMPONENT SIDE WITH WHITE NON-
CONDUCTIVE INK.
6. DRILL: ALL HOLES SHALL BE DRILLED +/- .003 INCH
WITH RESPECT TO CTR. OF DRILLED PAD.
ALL HOLES FINISHED SIZE AFTER PLATING.
7. DROP ALL UNUSED PADS ON INNER LAYERS.
8. DO NOT ALTER ARTWORK TO ADD LOGO OR DATE CODE BUT YOU MAY
MODIFY PAD SIZE TO MEET END FINISH.
9. PCB's SHOULD BE ROHS COMPLIANT.


10. SCORING:



Fabrication Drawing

<div>APPROVALS</div>		<div>LINEAR TECHNOLOGY</div>		1630 McCarthy Blvd. Milpitas, CA 95035 PH: (408)432-1900	
		<div>LT3751EUFD</div> <div>Capacitor Charger Controller with Regulation</div>			
DRAWN		INIT	DATE	<div>FD</div> <div>Demo Circuit 1322A</div> <div>REV. 1</div>	
CHECK					
DESIGN		RudYB			
ENGR		Wei Gu			
SCALE = NONE		<div>DES-23xxxx</div> <div>SHT 1 of 1</div>			

Demo Circuit 1322A
Linear Tech. Corp.



SIZE	QTY	SYM	PLATED	TOL
187	4	+	YES	+/-3MIL
35	9	X	YES	+/-3MIL
70	2	□	NO	+/-3MIL
10	90	◇	YES	+/-3MIL
94	9	X	YES	+/-3MIL
120	2	⋈	YES	+/-3MIL