



REVISION HISTORY				
ECO	REV	DESCRIPTION	APPROVAL	DATE
	3	THIRD PROTOTYPE	EDWIN L.	02/28/11


**NOTES: UNLESS OTHERWISE SPECIFIED,**

1. FAB PER IPC-A-600
2. MATERIAL--LEAD FREE ASSEMBLY COMPLIANT, ISOLA FR-370HR OR EQUIVALENT.
  - FINISHED THICKNESS TO BE  $1.6 \pm 0.13$
  - TOTAL OF 6 LAYERS WITH 2 OZ. CU ON THE OUTER LAYERS AND 1 OZ. CU ON THE INNER LAYERS.
  - FLAMMABILITY RATING: 94 V-0 MINIMUM .
3. SIZE: CUT TO DIMENSIONS AND TOLERANCES SHOWN.  
0.00 ARE PRIMARY DATUMS.
4. DRILLING: DRILL HOLES PER SCHEDULE. PLATE THROUGH HOLES WITH COPPER, 0.025 THICK MIN.  
ALL HOLE SIZES ARE SPECIFIED AFTER PLATING.  
HOLE LOCATION TOLERANCES ARE  $\pm 0.08$   
IN RELATION TO CENTER
5. FINISH: -SMORC USING LPI BOTH SIDES, COLOR GREEN.
  - GILD IMMERSION BOTH SIDES.
  - SILKSCREEN BOTH SIDES WITH WHITE NON-CONDUCTIVE INK.
6. DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.  
PAD SIZE CAN BE MODIFIED TO MEET END FINISH.
7. PCBs SHALL BE RoHS COMPLIANT.
8. SCORING FOR PANELIZED PCB (PRODUCTION FAB ONLY):




## LAYER STRUCTURE

SIZE	QTY	SYM	PLATED	TOL
0.25	376	+	YES	+/-0.08
0.762	4	×	YES	+/-0.08
1.62	9	□	YES	+/-0.08
1.78	2	◇	NO	+/-0.08
2.4	8	⊠	YES	+/-0.13

<p>UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS TOLERANCES ON ANGLE <math>\pm 1^\circ</math></p> <p>XX <math>\pm 0.25</math> XXX <math>\pm 0.127</math></p> <p>INTERPRET DIM AND TOL PER ASME Y14.5M-1994</p>	
THIRD ANGLE PROJECTION	DO NOT SCALE DRAWING

<b>APPROVALS</b>	<b>PCB DES.</b>	<b>MI</b>
	<b>APP. ENG.</b>	<b>EDWIN L.</b>
		<b>SCALE: NONE</b>

		1650 JACOBY BLVD FAY, CA 94504 PH: (415) 761-0000 WWW.LINEAR.COM LYTIC CONFIDENTIAL	
TITLE: FABRICATION DRAWING,			
DUAL MONOLITHIC STEP-DOWN CONVERTER			
SIZE	IC NO.	REV	
N/A	LT362AEIFE	3	
DEMO CIRCUIT 1403A		SHT 1 of 1	
FILENAME: 1557A-1.PCS			