


REVISIONS			
REV	DESCRIPTION	APPR	DATE
0	1st Prototype		

NOTES : Unless Otherwise Specified


1. FAB PER IPC-A-600.
2. MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4.  
2 OZ. COPPER FINISH ON EXTERNAL LAYERS.  
1 OZ. COPPER FINISH ON INTERNAL LAYERS.  
THICKNESS .062 +/- .006 TOTAL OF 4 LAYERS.  
FLAMMABILITY RATING: 94 V-0 MINIMUM .  
0.00 ARE PRIMARY DATUMS.
3. SIZE: DIMENSIONS SHOWN AND TOLERANCES +/-0.010  
0.00 ARE PRIMARY DATUMS.
4. DRILLING: DRILL HOLES PER SCHEDULE. PLATE THROUGH  
HOLES WITH COPPER, .001 INCH THICK MIN. ALL  
HOLE SIZES ARE SPECIFIED AFTER PLATING.  
HOLE LOCATION TOLERANCES ARE +/-3MIL  
INCH IN RELATION TO CENTER
5. FINISH: SMOBC USING LPI BOTH SIDES COLOR RED.  
GOLD IMMERSION BOTH SIDES.
6. SILKSCREEN : USING WHITE NON-CONDUCTIVE EPOXY INK.
7. DO NOT ALTER ARTWORK TO ADD LOGO OR DATE CODE BUT MAY  
MODIFY PAD SIZE TO MEET END FINISH.
8. PCB'S SHOULD BE RoHS COMPLIANT.

9. SCORING:



FABRICATION DRAWING

APPROVALS		LINEAR TECHNOLOGY 1630 McCardy Blvd. Milpitas, CA 95035 PH: (408)432-1900	
DRAWN	INIT	DATE	
CHECK			
DESIGN	Rudy/B		
ENGR	Jim Noon		
SCALE = NONE		Sheet 1 of 1	



SIZE	QTY	SYM	PLATED	TOL
94	17	+	YES	+/-3mil
70	2	X	NO	+/-3mil
63	4	□	YES	+/-3mil
31	15	◇	YES	+/-3mil
8	85	⊗	YES	+/-3mil
35	2	⊗	NO	+/-3mil