


REVISIONS			
REV	DESCRIPTION	APPR	DATE
A	PROTOTYPE RELEASE		




LINEAR TECHNOLOGY
 *DC1022A - LTC3210-1EUD
 MAIN/CAM LED Controller
 DATE: 10-12-05

SHOWN FROM COMPONENT SIDE

SIZE	QTY	SYM	PLTD
0.035	28	+	PLTD
0.037	6	D	PLTD
0.012	53	V	PLTD
0.064	4	W	PLTD
0.03	6	X	PLTD
0.07	2	Y	NPLTD
0.19	4	Z	PLTD


NOTES: UNLESS OTHERWISE SPECIFIED

1. FAB PER IPC-A-600
2. MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4
FINISHED THICKNESS TO BE 0.062" +/- .005"
WITH 2 OZ. COPPER ON THE OUTER LAYERS AND
1 OZ. COPPER ON THE INTERNAL LAYERS.
FLAMABILITY RATING: 94 V-0 MINIMUM .
3. SIZE: CUT TO DIMENSIONS AND TOLERANCES SHOWN.
4. DRILLING: DRILL HOLES PER SCHEDULE. PLATE THROUGH
HOLES WITH COPPER, 0.001" THICK MIN.
ALL HOLE SIZES ARE SPECIFIED AFTER PLATING.
HOLE LOCATION TOLERANCES ARE +/-0.003"
IN RELATION TO CENTER
5. FINISH: SMOBC USING LPI BOTH SIDES, COLOR GREEN.
WHITE TIN IMMERSION (OMIKRON).
FOR SILKSCREEN: USE WHITE NON-CONDUCTIVE INK.
6. DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
7. SCORING FOR PANELIZED PCB:



8. PLEASE LOOK AT THE README FILE FOR THE OTHER REQUIREMENTS.

Fabrication Drawing

APPROVALS			 1630 MCCATHY BLVD MILPITAS, CA 95035 PH: (408)432-1900 LTC CONFIDENTIAL- FOR CUSTOMER USE ONLY	
	INIT	DATE		
DRAWN	NICK C.	10-12-05	TITLE: FABRICATION DRAWING LTC3210-1EUD, MAIN/CAM LED Controller	
CHECK				
DESIGN				
ENGR				
			SIZE	REV.
			A	A
SCALE = NONE			DES- 0000	SHT 1 of 1