


SIZE	QTY	SYM	PLATED	TOL
70	2	+	NO	+/-0.003
187	4	X	YES	+/-0.003
35	17	□	YES	+/-0.003
10	34	◇	YES	+/-0.003
30	10	⊗	YES	+/-0.003
95	10	⊠	YES	+/-0.003
57	2	⊕ ^A	YES	+/-0.003
215	2	⊕ ^B	YES	+/-0.003

- NOTES: UNLESS OTHERWISE SPECIFIED**
- FAB PER IPC-A-600. PCBs ARE TO BE ROHS COMPLIANT.
 - MATERIAL: EPOXY FIBERGLASS; NEMA GRADE FR-4.
2 OZ. COPPER FINISH ON ALL LAYERS.
THICKNESS .062 +/- .006 TOTAL OF 2 LAYERS.
FLAMMABILITY RATING: 94 V-0 MINIMUM .
0.00 ARE PRIMARY DATUMS.
 - SIZE: DIMENSIONS AND TOLERANCES SHOWN.
 - DRILLING: DRILL HOLES PER SCHEDULE. PLATE THROUGH HOLES WITH COPPER, .001 INCH THICK MIN. ALL HOLE SIZES ARE SPECIFIED AFTER PLATING.
HOLE LOCATION TOLERANCES ARE +/- .003 INCH IN RELATION TO CENTER
 - FINISH: SMOBC USING LPI BOTH SIDES COLOR GREEN.
GOLD IMMERSION BOTH SIDES.
 - SILKSCREEN : USING WHITE NON-CONDUCTIVE EPOXY INK.
 - DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE
BUT YOU MAY MODIFY PAD SIZE TO MEET END FINISH.
 - SCORING: (FOR PRODUCTION RUN ONLY)



FAB DRAWING

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCES ON ANGLE ± 1
2 PLACE ± .01 3 PLACE ± .005
INTERPRET DIM AND TOL
PER ASME Y14.5M - 1994

APPROVALS

INIT	DATE
PCB DESIGNER J. Wu	7/23/08
ENGINEER A. Sevastopoulos	7/23/08
CHECK	



TITLE: LTC6909CMS

3- to 8- Output Multiphase Oscillator with SSFM

SIZE	DEM	REV.	A
A	DC1446A		

SHT 1 of 1