


REVISIONS		
REV	APPR	DATE

NOTES: UNLESS OTHERWISE SPECIFIED:


- ARTWORK P/N Demo Circuit 1094A
- FAB PER IPC-A-600. 4-Layers.
- MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4
.062 +/- .005 INCH THICKNESS WITH 2 OZ.
COPPER FINISH ON TWO OUTER LAYERS AND
1 OZ. COPPER ON TWO INTERNAL LAYERS.
FLAMABILITY RATING: 94 V-2 MINIMUM .
- SIZE: CUT TO DIMENSIONS AND TOLERANCES SHOWN.
- BOARD: SELECTIVE PLATED BOARD. SOLDER
MASK OVER BARE COPPER, COLOR, GREEN LPI.
WHITE TIN IMMERSION (OMIKRON) BOTH SIDES.
SILKSCREEN COMPONENT SIDE WITH WHITE NON-
CONDUCTIVE INK.
PLATE THRU ALL HOLES WITH COPPER
MIN. PLATING THICKNESS: 1 OZ. EXCEPT
WHERE PLATING NOT REQUIRED
- DRILL: ALL HOLES SHALL BE DRILLED +/- .003 INCH
WITH RESPECT TO CTR. OF DRILLED PAD.
ALL HOLES FINISHED SIZE AFTER PLATING.


- DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
- SCORING:



- DO NOT ALTER SOLDER MASK MAINTAIN .0005 (1/2 MIL) CLEARANCE
ON SMT PADS.

Fabrication Drawing

APPROVALS				 1630 McCarthy Blvd. Milpitas, CA 95035 PH: (408)432-1900	
DRAWN	INIT	DATE			
CHECK					
DESIGN	N/C	2/5/07	TITLE: Standalone Li-Ion Battery Charger		
ENGR	MM				
			SIZE	Demo Circuit 1094A	REV. A
			NONE		
SCALE = NONE			DES-23xxxx		
			SHT 1 of 1		



SIZE	QTY	SYM	PLATED	TOL
0.07	2	+	NO	+/-0.0
0.19	4	X	YES	+/-0.0
0.063	5	□	YES	+/-0.0
0.01	28	◇	YES	+/-0.0
0.031	9	⊗	YES	+/-0.0
0.094	4	⊗	YES	+/-0.0
0.0311	3	⊕	YES	+/-0.0
0.035	2	⊕	NO	+/-0.0
0.035	3	⊕	YES	+/-0.0