



REVISIONS		
REV	DESCRIPTION	DATE




NOTES : Unless Otherwise Specified

1. MATERIAL : FR4 OR EQUIVALENT EPOXY, 2 OZ. COPPER CLAD (Not Required for Prototype Boards).
THICKNESS .062 +/--.006 TOTAL OF 4 LAYERS.
2. FINISH : ALL PLATED HOLES .001 MIN. / .0015 MAX. COPPER PLATE
WHITE TIN IMMERSION (OMIKRON) BOTH SIDES, (Not Required for Prototype Boards).
BEFORE REFLOW, SOLDER MASK OVER BARE COPPER (SMOBC)
3. SOLDER MASK : BOTH SIDES USING GREEN LPI
4. SILKSCREEN : USING WHITE NON-CONDUCTIVE EPOXY INK
5. ALL DIMENSIONS ARE IN INCHES
6. SCORING: (Not Required for Prototype Boards).



SIZE	QTY	SYM	PLTD
70	2	X	NPLTD
94	7	□	PLTD
15	101	◇	PLTD
12	43	⊗	PLTD
35	4	⊗	PLTD

Fabrication Drawing

APPROVALS		<div>  <div> 1630 McCarthy Blvd. Milpitas, CA 95035 PH: (408)432-1900 </div> </div>	
DRAWN	INIT	DATE	
CHECK	KL		
DESIGN			
ENGR	KH		
SCALE = NONE		SHT 1 of 1	

2A, 38V Step-Down Switching Regulator with SYNC Function and EMC Filters			
SIZE	DEMO BRD	DC1212A-A/B	REV. A