



SHOWN FROM TOP SIDE



LAYER STRUCTURE




REVISION HISTORY

ECO	REV	DESCRIPTION	APP. ENG.	DATE
-	3	PRODUCTION	VLADIMIR O.	08-09-12



SIZE	QTY	SYM	PLATED	TOL
0.19	4	+	NO	+/-0.003"
0.07	3	X	NO	+/-0.003"
0.064	15	□	YES	+/-0.003"
0.094	14	◇	YES	+/-0.003"
0.012	308	⊗	YES	+/-0.003"
0.215	8	⊗	YES	+/-0.003"
0.035	7	+ ^A	YES	+/-0.003"

NOTES: UNLESS OTHERWISE SPECIFIED

- FAB PER IPC-A-600.
- MATERIAL: -LEAD FREE ASSEMBLY COMPLIANT, ISOLA FR-370HR OR EQUIVALENT.
-FINISHED THICKNESS TO BE 0.062" +/- .005"
-TOTAL OF 4 LAYERS WITH 2 OZ. CU ON THE OUTER LAYERS AND 1 OZ. CU ON THE INNER LAYERS.
-FLAMMABILITY RATING: 94 V-0 MINIMUM.
- SIZE: CUT TO DIMENSIONS AND TOLERANCES SHOWN.
0.00" ARE PRIMARY DATUMS.
- DRILLING: -DRILL HOLES PER SCHEDULE. PLATE THROUGH HOLES WITH COPPER, 0.001" THICK MIN.
-ALL HOLE SIZES ARE SPECIFIED AFTER PLATING.
-HOLE LOCATION TOLERANCES ARE +/-0.003" IN RELATION TO CENTER
- FINISH: -SMOBC USING LPI BOTH SIDES, COLOR GREEN.
-GOLD IMMERSION BOTH SIDES.
-FOR SILKSCREENS: USE WHITE NON-CONDUCTIVE INK.
- DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
PAD SIZE CAN BE MODIFIED TO MEET END FINISH.
- PCBS ARE TO BE RoHS COMPLIANT.
- SCORING FOR PANELIZED PCB (PRODUCTION FAB ONLY):



9. SUBJECT TO CHANGE BY MANUFACTURER, DEPENDING ON DIELECTRIC CONSTANT DEVIATIONS. PLEASE CONSULT LTC.

<div>UNLESS OTHERWISE SPECIFIED</div> <div>DIMENSIONS ARE IN INCHES</div> <div>TOLERANCES:</div> <div>0.XX" = ±0.01"</div> <div>0.XXX" = ±0.005"</div> <div>INTERPRET DIM AND TOL PER ASME Y14.5M-1994</div> <div>THIRD ANGLE PROJECTION</div> <div></div>	<div>APPROVALS</div>		<div><div>LINEAR TECHNOLOGY</div></div> <div>1630 MCCARTHY BLVD MILPITAS, CA 95035 PH: (408)432-1900 www.linear.com LTC CONFIDENTIAL- FOR CUSTOMER USE ONLY</div>
	PCB DES.	KIM T.	
	APP ENG.	VLADIMIR O.	
TITLE: FABRICATION DRAWING			
DUAL HOT SWAP CONTROLLER			
SIZE IC NO.		REV	
N/A LTC4226CUD-1/-2		3	
DEMO CIRCUIT 1627A			
SCALE = NONE		FILENAME: DC1627A-3.PCB	
		SHT 1 OF 1	