


Demo Circuit 1254A
Linear Tech. Corp.



SIZE	QTY	SYM	PLATED	TOL
187	4	+	YES	+/-3MIL
70	2	X	NO	+/-3MIL
94	18	□	YES	+/-3MIL
10	136	◇	YES	+/-3MIL
31	13	⊗	YES	+/-3MIL


REVISIONS

REV	APPR	DATE
-----	------	------


NOTES: UNLESS OTHERWISE SPECIFIED.

1. ARTWORK P/N DEMO CIRCUIT 1254A Rev2
2. FAB PER IPC-A-600. 6-Layers.
3. MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4 .062 +/- .005 INCH THICKNESS WITH 2 OZ. COPPER FINISH ON EXTERNAL LAYERS AND 1 OZ. COPPER ON FOUR INTERNAL LAYERS. FLAMMABILITY RATING: 94 V-2 MINIMUM .
4. SIZE: CUT TO DIMENSIONS AND TOLERANCES SHOWN. 0.00 ARE PRIMARY DATUMS.
5. BOARD: SELECTIVE PLATED BOARD. SOLDER MASK OVER BARE COPPER, COLOR, GREEN LPI. GOLD IMMERSION BOTH SIDES. SILKSCREEN COMPONENT SIDE WITH WHITE NON-CONDUCTIVE INK.
6. DRILL: ALL HOLES SHALL BE DRILLED +/- .003 INCH WITH RESPECT TO CTR. OF DRILLED PAD. ALL HOLES FINISHED SIZE AFTER PLATING.
7. DROP ALL UNUSED PADS ON INNER LAYERS.
8. DO NOT ALTER ARTWORK TO ADD LOGO OR DATE CODE BUT YOU MAY MODIFY PAD SIZE TO MEET END FINISH.
9. PCB's SHOULD BE RoHS COMPLIANT.

10. SCORING:



Fabrication Drawing

APPROVALS		 1630 McCarthy Blvd. Milpitas, CA 95035 PH: (408)432-1900	
DRAWN	INIT	DATE	
CHECK			
DESIGN	RudyB		
ENGR	Johans		
TITLE: LTC3853EUJ		Polyphase 3-Output Step-Down Supply with Tracking	
FD		Demo Circuit 1254A	REV. 2
SCALE = NONE		DES-23xxxx	SHT 1 of 1