



LAYER STRUCTURE




NOTES: UNLESS OTHERWISE SPECIFIED

1. FAB PER IPC-A-600.
2. MATERIAL: –EPOXY FIBERGLASS, NEMA GRADE FR-4
–FINISHED THICKNESS TO BE 0.062" \pm / – .0035"
–TOTAL OF 6 LAYERS WITH 2 OZ. CU ON THE LAYER 1,
LAYER 2, LAYER 5 AND LAYER 6.
–1 OZ. CU ON THE LAYER 3 AND LAYER 4
–FLAMMABILITY RATING: 94 V-0 MINIMUM.
3. SIZE: CUT TO DIMENSIONS AND TOLERANCES SHOWN.
0.00" ARE PRIMARY DATUMS.
4. DRILLING: –DRILL HOLES PER SCHEDULE. PLATE THROUGH
HOLES WITH COPPER, 0.001" THICK MIN.
–ALL HOLE SIZES ARE SPECIFIED AFTER PLATING.
–HOLE LOCATION TOLERANCES ARE \pm / –0.003"
IN RELATION TO CENTER
5. FINISH: –SNOBIC USING LPI BOTH SIDES, COLOR GREEN.
–GOLD IMMERSION BOTH SIDES.
–FOR SILKSREEN: BOTH SIDES USE WHITE NON-CONDUCTIVE INK.
6. DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
PAD SIZE CAN BE MODIFIED TO MEET END FINISH.
7. PCBs ARE TO BE ROHS COMPLIANT.
8. SCORING FOR PANELIZED PCB:



SIZE	QTY	SYM	PLATED	TOL
0.03543	12	+	YES	+/-0.003
0.01	709	×	YES	+/-0.003
0.035	44	□	YES	+/-0.003
0.07	2	◇	NO	+/-0.003
0.187	4	⊗	YES	+/-0.003
0.067	28	⊗	YES	+/-0.003
0.055	10	⊖ ^A	YES	+/-0.003
0.205	4	⊖ ^B	YES	+/-0.003
0.189	2	⊖ ^C	YES	+/-0.003
0.037	20	⊖ ^D	YES	+/-0.003

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES: 0.1XX = ±0.01" 0.0XX = ±0.005" INTERPRET DIM AND TOL PER ASME Y14.5M-1994 THIRD ANGLE PROJECTION		APPROVALS			1530 MCCARTHY BLVD SUITE 100 PH: (408) 432-3600 www.linear.com LINEAR TECHNOLOGY THE CUSTOMER USE ONLY
		PCB DES.	Hz		
		APP ENG.	YI S.		
		TITLE: FABRICATION DRAWING POLYPHASE DC/DC CONVERTER WITH DIGITAL PWR MANAGEMENT			
		SIZE	IC NO.	REV	
N/A	LTC3880EUJ	1			
SCALE = NONE FILE NAME= DC1740A-1PCB					