


REVISION HISTORY				
ECO	REV	DESCRIPTION	APPROVAL	DATE
	2	PRODUCTION	MIKE S.	06-29-11


## NOTES: UNLESS OTHERWISE SPECIFIED

1. WORKMANSHIP SHALL BE IN ACCORDANCE WITH IPC-A-610.
2. ASSEMBLY PROCESS SHALL INCLUDE: REFLOW SOLDER TOP SIDE SMD. MAXIMUM SOLDER TEMPERATURE IS 240 DEGREES CELSIUS.
3. PARTS TO OMIT WILL BE SPECIFIED ON THE BILL OF MATERIALS. LOCATIONS OF OMITTED PARTS SHALL BE FREE OF SOLDER. MASK THE SOLDER STENCIL WHERE SMT PARTS ARE OMITTED.
4. INSTALL SHUNTS AS SHOWN ON ASSY DRAWING.
5. DEPANELIZE BOARDS AFTER ASSEMBLY AND ROUTE-OUT THE BREAKOUT TABS ON FOUR SIDES OF THE BOARD EDGE.
6. DO NOT APPLY ANY KIND OF ASSEMBLY STAMP OR QA STAMP TO ANY BOARD.
7. INSTALL 4 STANDOFFS AT 4 LOCATIONS AS SHOWN BELOW:




SECTION A-A ROTATED 90 DEGREES (4X)  
SCALE: NONE

8. INSTALL HARDWARE AS SHOWN BELOW.



SECTION B-B ROTATED 90 DEGREES (6X)  
SCALE: NONE

APPROVALS		 LINEAR TECHNOLOGY		1630 MCCARTHY BLVD MILPITAS, CA 95035 PH: (408) 432-1900 www.linear.com LTC CONFIDENTIAL- FOR CUSTOMER USE ONLY	
PCB DES.	AK				
APP. ENG.	MIKE S.	TITLE: TOP ASSEMBLY DRAWING, DUAL OUTPUT 4-PHASE STEP-DOWN CONVERTER			
		SIZE N/A	IC NO	LTC3860EUH DEMO CIRCUIT 1755A	REV 2
SCALE: NONE		FILENAME: DC1755A-2.PCB			SHT 1 of 2

