



REVISIONS		
REV	APPR	DATE

NOTES: UNLESS OTHERWISE SPECIFIED:

- ARTWORK P/N Demo Circuit 1324A
- FAB PER IPC-A-600, 4-Layers.
- MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4 .062 +/- .005 INCH THICKNESS WITH 2 OZ. COPPER FINISH ON TWO OUTER LAYERS AND 1 OZ. COPPER ON TWO INTERNAL LAYERS. FLAMMABILITY RATING: 94 V-2 MINIMUM .
- SIZE: CUT TO DIMENSIONS AND TOLERANCES SHOWN.
- BOARD: SELECTIVE PLATED BOARD: SOLDER MASK OVER BARE COPPER, COLOR, GREEN LPI. SOFT WIRE BONDABLE GOLD. SILKSCREEN COMPONENT SIDE WITH WHITE NON-CONDUCTIVE INK. PLATE THRU ALL HOLES WITH COPPER MIN. PLATING THICKNESS: 1 OZ. EXCEPT WHERE PLATING NOT REQUIRED
- DRILL: ALL HOLES SHALL BE DRILLED +/- .003 INCH WITH RESPECT TO CTR. OF DRILLED PAD. ALL HOLES FINISHED SIZE AFTER PLATING.
- DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE OR ELECTRICAL TEST STAMP, BUT YOU MAY MODIFY PAD SIZE TO MEET END FINISH.
- SCORING FOR PANELIZED PCB: "PRODUCTION RUN ONLY"



- DO NOT ALTER SOLDER MASK MAINTAIN .0018" OVERSIZE ON SMT PADS. A .005" WEBBING IS REQUIRED BETWEEN SMD PADS.
- PCB'S ARE TO BE ROHS COMPLIANT.

Fabrication Drawing

SIZE	QTY	SYM	PLATED	TOL
180	4	+	YES	+/-0.003
70	2	X	NO	+/-0.003
84	8	□	YES	+/-0.003
10	17	◇	YES	+/-0.003
63	2	⊗	YES	+/-0.003
31	3	⊗	YES	+/-0.003

APPROVALS			
DRAWN	INIT	DATE	
CHECK	LMJ	9/19/07	
DESIGN			
ENGR			
TITLE: LTC3672BEDC-2 Fixed-Output 400mA Buck Regulator with Dual 150mA LDOs			
SIZE		NONE	REV. A
Demo Circuit 1324A		SHT 1 of 1	

