


REVISIONS			
REV	DESCRIPTION	APPR	DATE
0	1st Prototype		


NOTES : Unless Otherwise Specified


1. FAB PER IPC-A-600.
2. MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4.
2 OZ. COPPER FINISH ON EXTERNAL LAYERS.
1 OZ. COPPER FINISH ON INTERNAL LAYERS.
THICKNESS .062 +/- .006 TOTAL OF 4 LAYERS.
FLAMMABILITY RATING: 94 V-0 MINIMUM .
0.00 ARE PRIMARY DATUMS.
3. SIZE: DIMENSIONS SHOWN AND TOLERANCES +/- .010
4. DRILLING: DRILL HOLES PER SCHEDULE. PLATE THROUGH HOLES WITH COPPER, .001 INCH THICK MIN. ALL HOLE SIZES ARE SPECIFIED AFTER PLATING.
HOLE LOCATION TOLERANCES ARE +/- .3mil
INCH IN RELATION TO CENTER
5. FINISH: SMOBC USING LPI BOTH SIDES COLOR GREEN.
GOLD IMMERSION BOTH SIDES.
6. SILKSCREEN : USING WHITE NON-CONDUCTIVE EPOXY INK.
7. DO NOT ALTER ARTWORK TO ADD LOGO OR DATE CODE BUT MAY MODIFY PAD SIZE TO MEET END FINISH.
8. PCB's SHOULD BE RoHS COMPLIANT.

9. SCORING:



FABRICATION DRAWING

APPROVALS		 LINEAR TECHNOLOGY		1630 McCarthy Blvd. Milpitas, CA 95035 PH: (408) 432-1800	
		TITLE: LTC3417AEDHC-2 Dual Synchronous Step-Down Regulator			
DRAWN	INIT	DATE	FD	Demo Circuit 1336A	REV. 0
CHECK					
DESIGN	RudyB				
ENGR	Tom Gross				
SCALE = NONE			Sheet 1 of 1		



SIZE	QTY	SYM	PLATED	TOL
31	15	+	YES	+/-0.003
94	7	X	YES	+/-0.003
70	2	□	NO	+/-0.003
10	24	◇	YES	+/-0.003
26	4	⊗	YES	+/-0.003
34	6	⊗	YES	+/-0.003