



REVISIONS			
REV	DATE	APPR	DATE

NOTES: Unless Otherwise Specified

1. MATERIAL: 2 LAYERS, 0.062" THK. FR-4 GLASS EPOXY 2 OZ. COPPER CLAD.
2. PLATE THRU HOLES WITH COPPER .0014 MIN. THICKNESS. ALL HOLE SIZES IN HOLE TABLE ARE AFTER PLATING.
3. SILKSCREEN: WITH WHITE EPOXY NON-CONDUCTIVE INK.
4. NO SILKSCREEN ALLOWED ON PADS LANDS.
5. SOLDER MASK: LPI, GREEN.
6. NO BLOCK SOLDERMASKING OF PADS ROWS.
7. DO NOT MAKE CHANGES ON SILKSCREEN, SUCH AS COMPANY LOGO, QC STAMPS.
8. DO NOT PLATE TOOLING(3PLCS) AND SCORING(26PLCS) HOLES. (Reference Drawing Dwg No. DC205A)
9. SCORING:




Linear Tech. Corp.
Demo Board 328A
LTC187256



SIZE	QTY	SYM	PLTD
10	10	+	PLTD
70	2	X	NPLTD
61	5	◇	PLTD

Fabrication Drawing

APPROVALS					1630 McCarthy Blvd. Milpitas, CA 95035 Ph: (408)432-1900	
	INIT	DATE				
DRAWN						
CHECK						
DESIGN	Rmb					
ENGR						
			TITLE: SOT-23 Boost Controller			
		SIZE	NONE	Demo Board 328	REV. A	
SCALE = NONE			DES-230367		SHT 1 of 1	