



REVISION HISTORY			
ECO	REV	DESCRIPTION	APPR
-	1	PRODUCTION	Leo C
			DATE
			02/08/12

NOTES: UNLESS OTHERWISE SPECIFIED

1. FAB PER IPC-A-600.
2. MATERIAL: -EPOXY FIBERGLASS, NEMA GRADE FR-4  
-FINISHED THICKNESS TO BE 0.062" +/- .005"  
-TOTAL OF 4 LAYERS WITH 2 OZ. CU ON THE OUTER LAYERS  
AND 1 OZ. CU ON THE INNER LAYERS.  
-FLAMMABILITY RATING: 94 V-0 MINIMUM.  
3. SIZE: CUT TO DIMENSIONS AND TOLERANCES SHOWN.  
0.00" ARE PRIMARY DATUMS.
4. DRILLING: -DRILL HOLES PER SCHEDULE. PLATE THROUGH HOLES WITH COPPER, 0.001" THICK MIN.  
-ALL HOLE SIZES ARE SPECIFIED AFTER PLATING.  
-HOLE LOCATION TOLERANCES ARE +/-0.003" IN RELATION TO CENTER
5. FINISH: -SMOBC USING LPT BOTH SIDES, COLOR GREEN.  
-GOLD IMMERSION BOTH SIDES.  
-FOR SILKSCREEN: BOTH SIDES USE WHITE NON-CONDUCTIVE INK
6. DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.  
PAD SIZE CAN BE MODIFIED TO MEET END FINISH.
7. PCBs ARE TO BE RoHS COMPLIANT.
8. SCORING FOR PANELIZED PCB:




SIZE	QTY	SYM	PLATED	TOL
10	34	+	YES	+/-3Mil
70	2	X	NO	+/-3Mil
35	16	□	YES	+/-3Mil
63	8	⊗	YES	+/-3Mil
31	21	⊗	YES	+/-3Mil



LAYER 1 - TOP LAYER  
LINEAR TECHNOLOGY CORPORATION  
DC1338B-Rev1, LTC2990CMS  
DATE : 02/08/12

SHOWN FROM COMPONENT SIDE

LAYER STRUCTURE



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON ANGLE .10° 0.XX" = ±0.01" 0.XXX" = ±0.005" INTERPRET DIM AND TOL PER ASME Y14.5M-1994		APPROVALS		LINEAR TECHNOLOGY	
THIRD ANGLE PROJECTION 	PCB DES.	INT	DATE	1530 MCCARTHY BLVD HUNTINGTON BEACH, CA 92653 PH: (408)332-1900 LTC CONFIDENTIAL- FOR CUSTOMER USE ONLY	
	ENG.	RB	02/08/12		
		Leo C	02/08/12	TITLE: FABRICATION DRAWING TEMPERATURE, VOLTAGE AND CURRENT MONITOR	
				SIZE	REV.
				A	1
DO NOT SCALE DRAWING		SCALE: NONE		IC NO.	FILENAME:
				LTC2990CMS	DC1338B-Rev1.PCB
				DEMO CIRCUIT 1338B	SHT 1 of 1