



SIZE	QTY	SYM	PLTD
40	11	⊗	PLTD
15	379	T	PLTD
125	4	U	PLTD
70	2	V	NPLTD
35	37	W	PLTD
55	10	X	PLTD
190	6	Y	PLTD
94	9	Z	PLTD

Fabrication Drawing

NOTES : Unless Otherwise Specified

- MATERIAL : FR4 OR EQUIVALENT EPOXY, 2 OZ. COPPER CLAD
THICKNESS .062 +/- .006 TOTAL OF 6 LAYERS
- FINISH : ALL PLATED HOLES .001 MIN. / .0015 MAX. COPPER PLATE
ELECTRODEPOSITED TIN-LEAD COMPOSITION
BEFORE REFLOW , SOLDER MASK OVER BARE COPPER (SM08C)
- SOLDER MASK : BOTH SIDES USING LPI OR EQUIVALENT
- SILKSCREEN : USING WHITE NON-CONDUCTIVE EPOXY INK
- ALL DIMENSIONS ARE IN INCHES

- ART01 = LAYER 1 (COMPONENT SIDE)
- ART02 = LAYER 2 (PGND)
- ART03 = LAYER 3 (VIN+,V01+,V02+)
- ART04 = LAYER 4 (PGND,TRACE)
- ART05 = LAYER 5 (SGND,PGND)
- ART06 = LAYER 6 (SOLDER SIDE)