


SIZE	QTY	SYM	PLATED	TOL
70	2	+	NO	+/-3Mil
94	4	X	YES	+/-3Mil
35	4	□	YES	+/-3Mil
10	53	◇	YES	+/-3Mil
52	4	⊠	YES	+/-3Mil
59	1	⊠	YES	+/-3Mil
25	3	⊠	YES	+/-3Mil

NOTES : Unless Otherwise Specified

- FAB PER IPC-A-600.
- MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4.  
2 OZ. COPPER FINISH ON EXTERNAL LAYERS.  
1 OZ. COPPER FINISH ON INTERNAL LAYERS.  
THICKNESS .062 +/- .006 TOTAL OF 4 LAYERS.  
FLAMMABILITY RATING: 94 V-0 MINIMUM .
- SIZE: DIMENSIONS SHOWN AND TOLERANCES +/-0.010  
0.00 ARE PRIMARY DATUMS.
- DRILLING: DRILL HOLES PER SCHEDULE. PLATE THROUGH  
HOLES WITH COPPER, .001 INCH THICK MIN. ALL  
HOLE SIZES ARE SPECIFIED AFTER PLATING.  
HOLE LOCATION TOLERANCES ARE +/-3MIL  
INCH IN RELATION TO CENTER
- FINISH: SMOBC USING LPI BOTH SIDES COLOR GREEN.  
GOLD IMMERSION BOTH SIDES.
- SILKSCREEN : USING WHITE NON-CONDUCTIVE EPOXY INK.
- DO NOT ALTER ARTWORK TO ADD LOGO OR DATE CODE BUT MAY  
MODIFY PAD SIZE TO MEET END FINISH.
- PCB's SHOULD BE RoHS COMPLIANT.

9. SCORING:



Fabrication Drawing

APPROVALS		LINEAR TECHNOLOGY		1630 McCarthy Blvd. Milpitas, CA 95035 PH: (408)432-1900	
DRAWN	INIT	DATE			
CHECK	DESIGN	RmB			
ENGR	PHILPK				
TITLE: Resistor Set Oscillator in SOT-23					
FD	Demo Circuit 814A2	REV. 0			
SCALE = NONE			DES-24xxxx		
			SHT 1 of 1		