


LTC CONFIDENTIAL – For Customer Use Only




REVISION HISTORY				
ECO	REV	DESCRIPTION	DATE	APPROVED
	1	DEMO BOARD RELEASE	12/29/00	

HOLE SIZE CHART			
SYM	SIZE	QTY	PTH
+	.020+/- .003	58	YES
×	.035+/- .003	16	YES
□	.037+/- .003	9	YES
◇	.040+/- .003	13	YES
⊗	.070+/- .003	2	NO
⊗	.094+/- .003	5	YES
A	.120+/- .003	2	YES
B	.125+/- .003	4	YES
C	.205+/- .003	6	YES


NOTES: UNLESS OTHERWISE SPECIFIED

1. ARTWORK P/N DC358A REV 1.
2. FAB PER IPC-A-600
3. MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4  
FINISHED THICKNESS TO BE .062 +/- .005 INCH  
WITH 2 OZ. COPPER ON BOTH SIDES.  
FLAMABILITY RATING: 94 V-0 MINIMUM .
4. SIZE: CUT TO DIMENSIONS AND TOLERANCES SHOWN.  
.000 ARE PRIMARY DATUMS.
5. DRILLING: DRILL HOLES PER SCHEDULE. PLATE THROUGH HOLES  
WITH COPPER, .001 INCH THICK MIN. ALL HOLES SIZES  
ARE SPECIFIED AFTER PLATING.  
HOLES LOCATIONS TOLERANCES ARE +/- .003 INCH IN  
RELATION TO CENTER
6. FINISH: SMOBC USING WET MASK, OR LPI BOTH SIDES, GREEN  
PREFERRABLE. SILKSCREEN COMPONENT SIDE WITH WHITE  
NON-CONDUCTIVE INK.
7. DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
8. SCORING:



UNLESS OTHERWISE SPECIFIED  
DIMENSIONS ARE IN INCHES  
TOLERANCES ON ANGLE  $\pm 1^\circ$   
2 PLACE  $\pm .01$  3 PLACE  $\pm .005$   
INTERPRET DIM AND TOL  
PER ASME Y14.5M - 1994

THIRD ANGLE PROJECTION



DO NOT SCALE DRAWING

CONTRACT NO	
APPROVALS	DATE
DRAWN L.SANTOS	8/15/00
CHECKED	
APPROVED	
ENGINEER	



1630 McCarthy Blvd.  
Milpitas, CA 95035  
Phone: (408)432-1900  
Fax: (408)434-0507

TITLE

FAB, LTC2411, DIFFERENTIAL INPUT 24-BIT ADC PCB

SIZE	CAGE CODE	DWG NO	REV
A		DC358A	1
SCALE 1/1	FILENAME: 358Ar1.PCB	SHEET 1 OF 1	