


REVISIONS			
REV	DESCRIPTION	APPR	DATE
0	1st Prototype		

NOTES : Unless Otherwise Specified


1. FAB PER IPC-A-600.
2. MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4.
2 OZ. COPPER FINISH ON EXTERNAL LAYERS.
1 OZ. COPPER FINISH ON INTERNAL LAYERS.
THICKNESS .062 +/- .006 TOTAL OF 4 LAYERS.
FLAMMABILITY RATING: 94 V-0 MINIMUM .
0.00 ARE PRIMARY DATUMS.
3. SIZE: DIMENSIONS SHOWN AND TOLERANCES +/- 0.010
4. DRILLING: DRILL HOLES PER SCHEDULE. PLATE THROUGH HOLES WITH COPPER, .001 INCH THICK MIN. ALL HOLE SIZES ARE SPECIFIED AFTER PLATING.
HOLE LOCATION TOLERANCES ARE +/- 3MIL INCH IN RELATION TO CENTER
5. FINISH: SMOBC USING LPI BOTH SIDES COLOR GREEN.
GOLD IMMERSION BOTH SIDES.
6. SILKSCREEN : USING WHITE NON-CONDUCTIVE EPOXY INK.
7. DO NOT ALTER ARTWORK TO ADD LOGO OR DATE CODE BUT YOU MAY MODIFY PAD SIZE TO MEET END FINISH.
8. PCB's SHOULD BE RoHS COMPLIANT.

9. SCORING:




DEMO CIRCUIT 1401A
Linear Tech. Corp.

Component Side



SIZE	QTY	SYM	PLATED	TOL
70	2	+	NO	+/- 3Mils
94	5	X	YES	+/- 3Mils
10	28	◇	YES	+/- 3Mils
34	12	⊗	YES	+/- 3Mils

FABRICATION DRAWING

APPROVALS		 LINEAR TECHNOLOGY		1630 McCarthy Blvd. Milpitas, CA 95035 PH: (408)432-1900	
		DRAWN	DATE		
CHECK		DESIGN	RudyB	TITLE: LT3085EDCB	
ENGR		TYPEZ		Adjustable Single Resistor LDO Regulator	
				FD	REV. 0
SCALE = NONE		DEMO CIRCUIT 1401A		Sheet 1 of 1	