


REVISIONS			
REV	DESCRIPTION	APPR	DATE
A	PROTOTYPE RELEASE		


SIZE	QTY	SYM	PLTD
0.02	30	+	PLTD
0.07	2	×	NPLTD
0.035	6	□	PLTD
0.094	5	◇	PLTD

NOTES : Unless Otherwise Specified


1. MATERIAL : FR4 OR EQUIVALENT EPOXY, 2 OZ. COPPER CLAD
THICKNESS .062 +/- .006 TOTAL OF 4 LAYERS.
2. FINISH : ALL PLATED HOLES .001 MIN. / .0015 MAX. COPPER PLATE
ELECTRODEPOSITED TIN-LEAD COMPOSITION
BEFORE REFLOW , SOLDER MASK OVER BARE COPPER (SMOBC).
3. SOLDER MASK : BOTH SIDES USING LPI OR EQUIVALENT.
4. SILKSCREEN : USING WHITE NON-CONDUCTIVE EPOXY INK.
5. UNUSED SMD COMPONENTS SHOULD BE FREE OF SOLDER.
6. FILL UP ALL VIAS WITH SOLDER.
7. SCORING:



8. PLEASE LOOK AT THE README FILE FOR THE OTHER REQUIREMENTS.



SHOWN FROM COMPONENT SIDE

APPROVALS				LINEAR TECHNOLOGY	1630 McCarthy Blvd Milpitas, CA 95035 PH: (408)432-1900
	INIT	DATE			
DRAWN					
CHECK					
DESIGN	KIM T.	11-16-00			
ENGR	SAM N.	11-16-00	TITLE: Fabrication Drawing		
			100mA WHITE LED POWER SUPPLY		
			SIZE A DEMO DC381A-LTC3201		REV. A
SCALE = NONE			DES- 0000		SHT 1 of 1