


- ART01 = LAYER 1 (COMPONENT SIDE)
- ART02 = LAYER 2 (PRIMARY_SECONDARY GND)
- ART03 = LAYER 3 (SIGNAL3,PRIGND,GND)
- ART04 = LAYER 4 (SIGNAL4,+V01,PRIGND,GND)
- ART05 = LAYER 5 (PRIMARY_SECONDARY GND)
- ART06 = LAYER 6 (SOLDER SIDE)


NOTES : Unless Otherwise Specified

1. MATERIAL : FR4 OR EQUIVALENT EPOXY, 2 OZ. COPPER CLAD
THICKNESS .062 +/- .006 TOTAL OF 6 LAYERS
2. FINISH : ALL PLATED HOLES .001 MIN. / .0015 MAX. COPPER PLATE
ELECTRODEPOSITED TIN-LEAD COMPOSITION
BEFORE REFLOW , SOLDER MASK OVER BARE COPPER (SMOBC)
GOLD IMMERSION BOTH SIDES
3. SOLDER MASK : BOTH SIDES USING RED LPI
4. SILKSCREEN : USING WHITE NON-CONDUCTIVE EPOXY INK
5. ALL DIMENSIONS ARE IN INCHES
6. SCORING:



Fabrication Drawing

SIZE	QTY	SYM	PLTD
25	72	W	PLTD
94	8	X	PLTD
10	110	Y	PLTD
72	2	Z	NPLTD

<div>APPROVALS</div>				<div>LINEAR TECHNOLOGY</div>		1630 McCarthy Blvd. Milpitas, CA 95035 PH: (408)432-1900	
		DRAWN		INIT	DATE	TITLE: 48Vin to 3.3V, 25A Isolated DC/DC Converter LT1950EGN, LTC1698EGN, LTC1693-1CS8	
		CHECK					
		DESIGN		KWL			
		ENGR					
		SIZE	A	DEMO BRD	DC442	REV. A	
SCALE = NONE		DES- 0000			SHT 1 of 1		