


SIZE	QTY	SYM	PLATED	TOL
70	2	+	NO	+/-0.0
95	12	X	YES	+/-0.0
10	8	□	YES	+/-0.0
8	23	◇	YES	+/-0.0

NOTES: Unless Otherwise Specified:

- 1. PCBs Are To Be RoHS Compliant
- 2. Fab Per IPC-A-600
- 3. Material: Epoxy Fiberglass, NEMA Grade FR-4, 4 Layers  
.062 +/- .005 Inch Thickness With  
2 OZ. Copper Finished On All Outer Layers,  
1 OZ. Copper On All Internal Layers.  
Flammability Rating: 94 V-2 Minimum.
- 4. Size: Cut To Dimensions And Tolerances Shown.
- 5. Finish: SMOBC Using Wet Mask, Or LPI Both Sides, Color Green.  
Silkscreen Component Side With White Non-conductive Ink.  
Gold Immersion Both Sides (Not Required For Prototype Boards)
- 6. Drilling: Drill Holes Per Schedule. Plate Through  
Holes With Copper, .001 Inch Thick Min. All  
Hold Sizes Are Specified After Plating.  
Holes Location Tolerances Are +/- .003" In Relation To Center.
- 7. Do Not Alter Artwork To Add Logo Or Date Code,  
You May Modify Pad Size To Meet End Finish.
- 8. Scoring: (Not Required For Prototype Boards)



Fabrication Drawing

APPROVALS

DRAWN	INIT	DATE
CHECK	KL	
DESIGN		
ENGR	KS	
SCALE = NONE		

LINEAR TECHNOLOGY

1630 McCarthy Blvd.  
Milpitas, CA 95035  
PH: (408)432-1900

LT3519EMS  
4W LED Driver

SIZE	DEMO BRD	REV.
A	DC1482A	A

SH T 1 of 1