




REVISIONS		
REV	DESCRIPTION	DATE



- NOTES: UNLESS OTHERWISE SPECIFIED
1. FAB PER IPC-A-600
 2. MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4
FINISHED THICKNESS TO BE .062 +/- .005 INCH
WITH 2 OZ. COPPER ON TWO OUTER LAYERS AND
1 OZ. COPPER ON TWO INTERNAL LAYERS.
FLAMABILITY RATING: 94 V-0 MINIMUM.
 3. SIZE: CUT TO DIMENSIONS AND TOLERANCES SHOWN.
0.00 ARE PRIMARY DATUMS.
 4. DRILLING: DRILL HOLES PER SCHEDULE. PLATE THROUGH
HOLES WITH COPPER, .001 INCH THICK MIN. ALL
HOLE SIZES ARE SPECIFIED AFTER PLATING.
HOLE LOCATION TOLERANCES ARE +/- .003
INCH IN RELATION TO CENTER
 5. FINISH: SMOBC USING WET MASK, OR LPI BOTH SIDES, GREEN
PREFERRABLE. SILKSCREEN COMPONENT SIDE WITH
WHITE NON-CONDUCTIVE INK.
 6. CONTROLLED 50 OHM IMPEDANCE (AT 2.5 GHz FREQ.) FOR LAYER 1-2.
7. SUBJECT TO CHANGE BY MANUFACTURER, DEPENDING ON DIELECTRIC
CONSTANT DEVIATIONS. PLEASE CONSULT LTC.
 8. DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.

SIZE	QTY	SYM	PLTD
95	8	+	PLTD
120	2	X	PLTD
10	278	□	PLTD
65	4	◇	PLTD
70	2	⊗	NPLTD

FAB DRAWING

APPROVALS		 LINEAR TECHNOLOGY		1630 McCarthy Blvd. Milpitas, CA 95035 PH: (408)432-1900	
DRAWN	INIT	DATE			
CHECK					
DESIGN	JUNE WU	10/19/01	TITLE: LT5506EUF, IF RECEIVER		
ENGR					
			SIZE	DEMOS	REV.
			A	DC468A	A
SCALE = NONE			DES-260011		SHT 1 of 1

