




SIZE	QTY	SYM	PLATED	TOL
0.254	61	+	YES	+/-0.08
1.8	2	X	NO	+/-0.13
2.4	5	□	YES	+/-0.13



REVISION HISTORY			
ECO	REV	DESCRIPTION	DATE
	2	Production	07/02/10

NOTES: UNLESS OTHERWISE SPECIFIED,

1. FAB PER IPC-A-600
2. MATERIAL: -EPOXY FIBERGLASS, NEMA GRADE FR-4  
-FINISHED THICKNESS TO BE 1.6mm +/- 0.127mm  
-TOTAL OF 4 LAYERS WITH 2 OZ. CU ON THE OUTER LAYERS AND 1 OZ. CU ON THE INNER LAYERS.  
-FLAMMABILITY RATING: 94 V-0 MINIMUM.
3. SIZE: CUT TO DIMENSIONS AND TOLERANCES SHOWN.  
0.00" ARE PRIMARY DATUMS.
4. DRILLING: DRILL HOLES PER SCHEDULE. PLATE THROUGH HOLES WITH COPPER, 0.0254mm THICK MIN.  
ALL HOLE SIZES ARE SPECIFIED AFTER PLATING.  
HOLE LOCATION TOLERANCES ARE +/-0.08mm IN RELATION TO CENTER
5. FINISH: -SMOBC USING LP1 BOTH SIDES, COLOR GREEN.  
-GOLD IMMERSION BOTH SIDES.  
-SILKSCREEN BOTH SIDES WITH WHITE NON-CONDUCTIVE INK.
6. DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.  
PAD SIZE CAN BE MODIFIED TO MEET END FINISH.
7. PCBs ARE TO BE RoHS COMPLIANT.

<div>UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS TOLERANCES ON ANGLE ±1° XX ± 0.254 XXX ± 0.127 INTERPRET DIM AND TOL PER ASME Y14.5M-1994 THIRD ANGLE PROJECTION</div>		APPROVALS		<div> LINEAR TECHNOLOGY</div> <div>1630 MCCARTHY BLVD MILPITAS, CA 95035 PH: (408)482-1800 WWW.LINEAR.COM LTC CONFIDENTIAL FOR CUSTOMER USE ONLY</div>			
		PCB DES.	MI				
		APP. ENG.	Zhongming Y.				
		TITLE: FABRICATION DRAWING: ISOLATED MONOLITHIC FLYBACK CONVERTER					
<div></div>		SIZE	IC NO	REV			
		N/A	LT3575EFE	DEMO CIRCUIT 1843A		2	
DO NOT SCALE DRAWING		SCALE: NONE		FILENAME: 1643A-1.PCB		SHT 1 of 1	