



REVISIONS			
REV	DESCRIPTION	APPR	DATE
A	PROTOTYPE RELEASE		


NOTES : Unless Otherwise Specified

1. FAB PER IPC-A-600.
2. MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4.
.062 +/- .005 INCH THICKNESS WITH 2 OZ.
COPPER FINISHED ON 4 LAYERS.
FLAMABILITY RATING: 94 V-0 MINIMUM .
3. DRILLING: DRILL HOLES PER SCHEDULE. PLATE THROUGH HOLES WITH COPPER, .001 INCH THICK MIN. ALL HOLE SIZES ARE SPECIFIED AFTER PLATING.
HOLE LOCATION TOLERANCES ARE +/- .003 INCH IN RELATION TO CENTER
4. SOLDER MASK : SMOBC USING LPI BOTH SIDES COLOR GREEN.
5. SILKSCREEN : USING WHITE NON-CONDUCTIVE EPOXY INK.
6. DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
7. SCORING:



SIZE	QTY	SYM	PLTD
10	34	+	PLTD
95	6	X	PLTD
35	3	□	PLTD
70	2	◇	NPLTD

FAB DRAWING

APPROVALS			 LINEAR TECHNOLOGY		1630 McCarthy Blvd. Milpitas, CA 95035 PH: (408)432-1900	
DRAWN		INIT	DATE			
CHECK						
DESIGN		JUNE WU	2/25/02		TITLE: LT1767EMS8E	
ENGR		Keith S.	2/25/02		Wide Input Range Step Down Converter	
			SIZE	A	DC502A	REV. A
				DEMO		
SCALE = NONE			DES-230532		SHT of 1	