



1



SIZE	QTY	SYM	PLTD	TOL
10	5	+	YES	+/-0.003
20	7	×	YES	+/-0.003
70	2	□	NO	+/-0.005
95	7	◇	YES	+/-0.01
120	4	⊗	YES	+/-0.01



1. ARTWORK P/N DC536A REV 1.
2. FAB PER IPC-A-600
3. MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4
FINISHED THICKNESS TO BE .062 +/- .005 INCH
WITH 2 OZ. COPPER ON TWO OUTER LAYERS AND
1 OZ. COPPER ON TWO INTERNAL LAYERS.
FLAMABILITY RATING: 94 V-2 MINIMUM .
4. SIZE: CUT TO DIMENSIONS AND TOLERANCES SHOWN.
0.00 ARE PRIMARY DATUMS.
5. BOARD: SELECTIVE PLATED BOARD. SOLDER
MASK OVER BARE COPPER.
WHITE TIN BOTH SIDES.
SOLDER MASK TYPE: WET PHOTO-IMAGEABLE
THE PCB COLOR: GREEN
SILKSCREEN COMPONENT SIDE WITH WHITE NON-
CONDUCTIVE INK.
PLATE THRU ALL HOLES WITH COPPER
MIN. PLATING THICKNESS: 1 OZ. EXCEPT
WHERE PLATING NOT REQUIRED
6. DRILL: ALL HOLES SHALL BE DRILLED +/- .003 INCH
WITH RESPECT TO CTR. OF DRILLED PAD.
ALL HOLES FINISHED SIZE AFTER PLATING.
7. DROP ALL UNUSED PADS ON INNER LAYERS.
8. DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
9. SCORING:

CONTRACT NO

APPROVALS		DATE
DRAWN	MEI	05-15-02
CHECKED		
APPROVED		
ENGINEER		

DO NOT SCALE DRAWING

1630 McCarthy Blvd.
Milpitas, CA 95035
Phone: (408)432-1900
Fax: (408)434-0507

TITLE

FAB, LTC4211CMS HOTSWAP MULTIFUNCTION
CURRENT CONTROL

SIZE A	CAGE CODE	DWG NO DC536A	REV 1
SCALE 1/1		FILENAME: 536A-1.PCB	SHEET 1 OF 1