


REVISION HISTORY				
ECO	REV	DESCRIPTION	APPROVED	DATE
	1	1ST PROTOTYPE	YI S.	02/03/11



NOTES:UNLESS OTHERWISE SPECIFIED.

- DO NOT APPLY LOAD FROM THE VO1+ TO VO1- OR FROM THE VO2+ TO VO2- TURRETS. THESE ARE ONLY INTENDED TO KELVIN SENSE THE OUTPUT VOLTAGE ACROSS COUT1 AND COUT4.

[2]	ASSY		FSW	R10	L1, L2	RS1, RS2	R45, R51	R61, R62	R29, R30, R39, R40	C14, C15	C41, C44	R31, R35
	- A	R SENSE	400kHz	102k	VITEC 59PR9875, 0.4uH	0.002	OPT	OPT	100	1nF	1nF	5.9k
	- B	DCR SENSE	300kHz	75k	VISHAY IHLP4040DZ11, 0.56uH	0	1.58k	0	OPT	220nF	1.5nF	5.9k

- ALL CAPACITORS AND RESISTORS ARE 0603.

CUSTOMER NOTICE

LINEAR TECHNOLOGY HAS MADE A BEST EFFORT TO DESIGN A CIRCUIT THAT MEETS CUSTOMER-SUPPLIED SPECIFICATIONS; HOWEVER, IT REMAINS THE CUSTOMER'S RESPONSIBILITY TO VERIFY PROPER AND RELIABLE OPERATION IN THE ACTUAL APPLICATION. COMPONENT SUBSTITUTION AND PRINTED CIRCUIT BOARD LAYOUT MAY SIGNIFICANTLY AFFECT CIRCUIT PERFORMANCE OR RELIABILITY. CONTACT LINEAR TECHNOLOGY APPLICATIONS ENGINEERING FOR ASSISTANCE.

THIS CIRCUIT IS PROPRIETARY TO LINEAR TECHNOLOGY AND SUPPLIED FOR USE WITH LINEAR TECHNOLOGY PARTS.

CONTRACT NO.

APPROVALS

PCB DES. MI

ENG. YI S.



1630 McCarthy Blvd.
Milpitas, CA 95035
Phone: (408)432-1900
Fax: (408)434-0507
LTC Confidential-For Customer Use Only

TITLE: SCHEMATIC
DUAL PHASE / DUAL OUTPUT SYNCHRONOUS
BUCK CONVERTER

SIZE N/A IC NO. LTC3869EUFD
REV 1

DATE: Tuesday, February 22, 2011 SHEET 1 OF 1