



| SIZE | QTY | SYM | PLTD  |
|------|-----|-----|-------|
| 95   | 5   | +   | PLTD  |
| 35   | 3   | X   | PLTD  |
| 15   | 41  | □   | PLTD  |
| 70   | 2   | ◇   | NPLTD |

NOTES : Unless Otherwise Specified

1. FAB PER IPC-A-600.
2. MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4.  
2 OZ. COPPER FINISHED ON OUTER LAYERS.  
1 OZ. COPPER FINISHED ON INNER LAYERS.  
THICKNESS .062 +/- .006 TOTAL OF 4 LAYERS.  
FLAMABILITY RATING: 94 V-0 MINIMUM .
3. DRILLING: DRILL HOLES PER SCHEDULE. PLATE THROUGH HOLES WITH COPPER. .001 INCH THICK MIN. ALL HOLE SIZES ARE SPECIFIED AFTER PLATING.  
HOLE LOCATION TOLERANCES ARE +/- .003 INCH IN RELATION TO CENTER
4. FINISH: SMOBC USING LPI BOTH SIDES COLOR GREEN.  
WHITE TIN IMMERSION (OMIKRON) BOTH SIDES.
5. SILKSCREEN : USING WHITE NON-CONDUCTIVE EPOXY INK.
6. DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
7. SCORING:



FAB DRAWING

|           |         |   |       |  |            |
|-----------|---------|---|-------|--|------------|
| APPROVALS |         |  LINEAR TECHNOLOGY |       | 1630 McCarthy Blvd.<br>Milpitas, CA 95035<br>PH: (408)432-1900 |            |
| DRAWN     | INIT    | DATE  |       |  |            |
| CHECK     | JUNE WU | 7/16/02   |       |  |            |
| DESIGN    | From H. | 7/16/02   |       |  |            |
| ENGR      |         |   |       |  |            |
|           |         |   | SIZE  | DC551A   | REV. A     |
|           |         |   | SCALE | DES-230566   |            |
|           |         |   |       |  | SHT 1 of 1 |