



REVISIONS			
REV	DESCRIPTION	APPR	DATE
A	PROTOTYPE RELEASE		

NOTES : Unless Otherwise Specified


1. FAB PER IPC-A-600.
2. MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4.  
.062 +/- .005 INCH THICKNESS WITH 2 OZ.  
COPPER FINISHED ON 2 LAYERS.  
FLAMABILITY RATING: 94 V-0 MINIMUM .
3. DRILLING: DRILL HOLES PER SCHEDULE. PLATE THROUGH  
HOLES WITH COPPER, .001 INCH THICK MIN. ALL  
HOLE SIZES ARE SPECIFIED AFTER PLATING.  
HOLE LOCATION TOLERANCES ARE +/- .003  
INCH IN RELATION TO CENTER
4. SOLDER MASK : SMOBC USING LPI BOTH SIDES COLOR GREEN.
5. SILKSCREEN : USING WHITE NON-CONDUCTIVE EPOXY INK.
6. DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.

7. SCORING:



SIZE	QTY	SYM	PLTD
95	7	+	PLTD
35	6	X	PLTD
70	2	□	NPLTD
10	24	◇	PLTD

FAB DRAWING

APPROVALS			 LINEAR TECHNOLOGY		1630 McCarthy Blvd. Milpitas, CA 95035 Ph: (408)432-1900	
	INIT	DATE				
DRAWN						
CHECK						
DESIGN	JUNE WU	10/4/02	TITLE: LTC3252EDE, Dual, Spread-Spectrum, Low Noise, Inductorless, Step Down DC/DC Converter			
ENGR	Bill Walter	10/4/02				
			SIZE	A	REV.	A
			DEMO	DEMO CIRCUIT 611A		
SCALE = NONE			DES-230580		SHT 1 of 1	