


SIZE	QTY	SYM	PLTD	TOL
10	18	⊗	YES	+/-0.0
15	22	⊗	YES	+/-0.0
35	11	+	YES	+/-0.0
40	2	□	YES	+/-0.0
72	2	⊗	NO	+/-0.0
95	13	◇	YES	+/-0.0

- ART01 = LAYER 1 (COMPONENT SIDE)
- ART02 = LAYER 2 (GND)
- ART03 = LAYER 3 (SIGNAL)
- ART04 = LAYER 4 (SOLDER SIDE)

NOTES : Unless Otherwise Specified

- MATERIAL : FR4 OR EQUIVALENT EPOXY, 2 OZ. COPPER CLAD
THICKNESS .062 +/--.006 TOTAL OF 4 LAYERS
- FINISH : ALL PLATED HOLES .001 MIN. / .0015 MAX. COPPER PLATE
ELECTRODEPOSITED TIN-LEAD COMPOSITION
BEFORE REFLOW , SOLDER MASK OVER BARE COPPER (SNOBC)
- SOLDER MASK : BOTH SIDES USING LPI OR EQUIVALENT
- SILKSCREEN : USING WHITE NON-CONDUCTIVE EPOXY INK
- ALL DIMENSIONS ARE IN INCHES
- SCORING:



Fabrication Drawing

APPROVALS		LINEAR TECHNOLOGY		1630 McCarthy Blvd. Milpitas, CA 95035 PH: (408)432-1900	
DRAWN	INIT	DATE			
CHECK					
DESIGN					
ENGR					
TITLE: 12C Controllable Buck Regulator					
SIZE	A	DC998A LTC3445EUF	REV.		
SCALE = NONE			DES- SHT 1 of 1		