



REVISIONS			
REV	DESCRIPTION	APPR	DATE



- ART01 = LAYER 1 (COMPONENT SIDE)
- ART02 = LAYER 2 (GND)
- ART03 = LAYER 3 (SIGNAL)
- ART04 = LAYER 4 (SOLDER SIDE)

NOTES : Unless Otherwise Specified

- MATERIAL : FR4 OR EQUIVALENT EPOXY, 2 OZ. COPPER CLAD
THICKNESS .062 +/- .006 TOTAL OF 4 LAYERS
- FINISH : ALL PLATED HOLES .001 MIN. / .0015 MAX. COPPER PLATE
ELECTRODEPOSITED TIN-LEAD COMPOSITION
BEFORE REFLOW , SOLDER MASK OVER BARE COPPER (SMOBC)
- SOLDER MASK : BOTH SIDES USING LPI OR EQUIVALENT
- SILKSCREEN : USING WHITE NON-CONDUCTIVE EPOXY INK
- ALL DIMENSIONS ARE IN INCHES
- SCORING:



SIZE	QTY	SYM	PLTD
20	2	+	PLTD
40	15	X	PLTD
10	22	X	PLTD
70	2	Y	NPLTD
95	7	Z	PLTD

Fabrication Drawing

APPROVALS		LINEAR TECHNOLOGY		1630 McCarthy Blvd. Milpitas, CA 95035 PH: (408)432-1900	
		TITLE: LTC3407EDD Dual Synchronous Step-Down DC/DC Converter		SIZE A	
DRAWN	INIT	DATE	DES	DC701A	REV.
CHECK					
DESIGN					
ENGR					
SCALE = NONE		DES-		SHT 1 of 1	