


NOTES : Unless Otherwise Specified


- 1. FAB PER IPC-A-600.
- 2. MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4.
 - 4 OZ. COPPER FINISHED ON OUTER LAYERS.
 - 2 OZ. COPPER FINISHED ON INNER LAYERS.
- THICKNESS .062 +/- .006 TOTAL OF 6 LAYERS.
- FLAMABILITY RATING: 94 V-0 MINIMUM .
- 3. SIZE: DIMENSIONS AND TOLERANCES SHOWN.
 - 0.00 ARE PRIMARY DATUMS.
- 4. DRILLING: DRILL HOLES PER SCHEDULE. PLATE THROUGH HOLES WITH COPPER. .001 INCH THICK MIN. ALL HOLE SIZES ARE SPECIFIED AFTER PLATING.
- HOLE LOCATION TOLERANCES ARE +/- .003 INCH IN RELATION TO CENTER
- 5. SOLDER MASK : SMOBC USING LPI BOTH SIDES COLOR GREEN.
- 6. SILKSCREEN : USING WHITE NON-CONDUCTIVE EPOXY INK.
- 7. DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
- 8. SCORING:



FAB DRAWING

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCES ON ANGLE ±1
2 PLACE ±.01 3 PLACE ±.005
INTERPRET DIM AND TOL
PER ASME Y14.5M - 1994

APPROVALS	
ENGR	INIT DATE
Ryan Huff	3/12/04
LAYOUT	J. Wu 3/12/04
SCALE = NONE	



1630 McCarthy Blvd.
Milpitas, CA 95035
PH: (408)432-1900

TITLE: LTC3705EGN, LTC3706EGN,
36V to 72Vin, Forward Converter

SIZE A DEMO DC776A REV. A

DES-230677 SHT 1 of 1

SIZE	QTY	SYM	PLTD
95	2	X	PLTD
65	4	□	PLTD
195	2	◇	PLTD
10	358	⊗	PLTD
70	2	A	NPLTD
187	4	B	PLTD

776A.pcb - Fri Jun 24 13:59:42 2005