


#### NOTES: UNLESS OTHERWISE SPECIFIED

1. WORKMANSHIP SHALL BE IN ACCORDANCE WITH IPC-A-810.
2. ASSEMBLY PROCESS SHALL INCLUDE: REFLOW SOLDER TOP SIDE SMD.
3. MAXIMUM SOLDER TEMPERATURE IS 240 DEG. C.
4. PARTS TO OMIT WILL BE SPECIFIED ON THE BILL OF MATERIALS.
5. LOCATIONS OF OMITTED PARTS SHALL BE FREE OF SOLDER.
6. MASK THE SOLDER STENCIL WHERE SMT PARTS ARE OMITTED.
7. INSTALL SHUNTS AS SHOWN.
8. DEPANALIZE BOARDS AFTER ASSEMBLY AND ROUTE-OUT THE BREAKOUT TABS ON FOUR SIDES OF THE BOARD EDGE.
9. DO NOT APPLY ANY KIND OF ASSEMBLY STAMP OR QA STAMP TO ANY BOARD.



		165 MCCARTHY BLVD FARMINGHAM, MA 01904 TEL: (408) 432-1900 FAX: (408) 432-1900 www.linear.com LTC CONFIDENTIAL - FOR CUSTOMER USE ONLY	
APPROVALS	DATE	TITLE:	
DRAWN MI	11/26/12	ASSY, LTC3787EUF, HIGH CURRENT 4-PHASE	
CHECKED JOSHUA Y.	01/22/13	SYNCHRONOUS BOOST CONVERTER	
APPROVED		SIZE	DWG. NO.
DESIGN		N/A	DEMO CIRCUIT 2001A
		SCALE: NONE	FILE: 2001b-1.PCB
			SHT 1 of 2