


REVISION HISTORY			
ECO	REV	DESCRIPTION	APPROVAL
	1	REBUILD WITH CHANGES	KAUNG H.
			DATE
			02/17/11

NOTES: UNLESS OTHERWISE SPECIFIED,

1. FAB PER IPC-A-600
2. MATERIAL: -LEAD FREE ASSEMBLY COMPLIANT, ISOLA FR-370HR OR EQUIVALENT.
-FINISHED THICKNESS TO BE .062 ± .005
-TOTAL OF 4 LAYERS WITH 2 OZ. CU ON THE OUTER LAYERS AND 1 OZ. CU ON THE INNER LAYERS.
-FLAMMABILITY RATING: 94 V-0 MINIMUM .
0.00 ARE PRIMARY DATUMS.
3. SIZE: CUT TO DIMENSIONS AND TOLERANCES SHOWN.
4. DRILLING: DRILL HOLES PER SCHEDULE. PLATE THROUGH HOLES WITH COPPER .001 THICK MIN.
ALL HOLE SIZES ARE SPECIFIED AFTER PLATING.
HOLE LOCATION TOLERANCES ARE ± .003 IN RELATION TO CENTER
5. FINISH: -SMOBC USING LPI BOTH SIDES, COLOR GREEN.
-GOLD IMMERSION BOTH SIDES.
-SILKSCREEN BOTH SIDES WITH WHITE NON-CONDUCTIVE INK
6. DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
PAD SIZE CAN BE MODIFIED TO MEET END FINISH.
7. PCBs SHALL BE RoHS COMPLIANT.
8. SCORING FOR PANELIZED PCB (PRODUCTION FAB ONLY):



SHOWN FROM TOP SIDE

SIZE	QTY	SYM	PLATED	TOL
10	28	X	YES	+/-0.003
20	44	□	YES	+/-0.003
35	41	+	YES	+/-0.003
40	6	⊗	YES	+/-0.003
62	2	◇	YES	+/-0.005
62	2	⊠	NO	+/-0.005
70	2	⊠	NO	+/-0.005
95	16	⊠	YES	+/-0.005
126	4	⊠	NO	+0.01/-0.001
187	4	⊠	NO	+/-0.01

LAYER STRUCTURE

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCES ON ANGLE ±1°
XX ±.01
XXX ±.006
INTERPRET DIM AND TOL
PER ASME Y14.5M-1994
THIRD ANGLE PROJECTION

APPROVALS

PCB DES.	MI
APP. ENG.	KAUNG H.

1650 MCCARTHY BLVD
SUITE 100
PHILADELPHIA, PA 19104
www.linear.com
LTC CONFIDENTIAL
FOR CUSTOMER USE ONLY

TECHNOLOGY

TITLE: FABRICATION DRAWING,
RJ-45 ETHERNET OUTPUT

SIZE	IC No.	REV
N/A	LTC4267CDHC	1

FILENAME: 804b-1.PCB

SHT 1 of 1