




ECO	REV	DESCRIPTION	APPROVAL	DATE
	1	PRODUCTION	KEITH S.	Feb 08, 2013

NOTES: UNLESS OTHERWISE SPECIFIED,



1. FAB PER IPC-A-600
2. MATERIAL: -EPOXY FIBERGLASS, NEMA GRADE FR-4
-FINISHED THICKNESS TO BE $1.6\text{mm} \pm 0.127\text{mm}$
-TOTAL OF 4 LAYERS WITH 2 OZ. CU ON THE
OUTER LAYERS AND 1 OZ. CU ON THE INNER LAYERS.
-FLAMMABILITY RATING: 94 V-0 MINIMUM .
3. SIZE: CUT TO DIMENSIONS AND TOLERANCES SHOWN.
0.00" ARE PRIMARY DATUMS.
4. DRILLING: DRILL HOLES PER SCHEDULE. PLATE THROUGH
HOLES WITH COPPER, 0.0254mm THICK MIN.
ALL HOLE SIZES ARE SPECIFIED AFTER PLATING.
HOLE LOCATION TOLERANCES ARE $\pm 0.08\text{mm}$
IN RELATION TO CENTER
5. FINISH: -SMOBC USING LP1 BOTH SIDES. COLOR GREEN.
-GOLD IMMERSE BOTH SIDES.
-SILKSCREEN COMPONENT SIDE WITH WHITE
NON-CONDUCTIVE INK.
6. DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
PAD SIZE CAN BE MODIFIED TO MEET END FINISH.
7. PCBs ARE TO BE RoHS COMPLIANT.
8. SCORING:



SIZE	QTY	SYM	PLATED	TOL
2.413	9	+	YES	+/-3Mils
0.2032	34	X	YES	± 0.08
1.651	7	□	YES	+/-3Mils
1.778	2	◇	NO	± 0.08
0.635	23	⊗	YES	± 0.08
0.15	47	⊗	YES	± 0.08



LAYER CONSTRUCTION

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS TOLERANCES ON ANGLE A 1° XXXX 0.25 XXXX 0.127 INTERPRET DIM AND TOL PER ASME Y14.5M-1984 THIRD ANGLE PROJECTION	APPROVALS				1850 MCCARTHY BLVD FORTYFIVE, CA 95006 TEL: 415.444.1100 WWW.LINEAR.COM LTC CONFIDENTIAL- FOR CUSTOMER USE ONLY
	PCB DES.	✕B			
	APP. ENG.	KEITH S.			
	SIZE	IC NO	REV	1	
DO NOT SCALE DRAWING	SCALE: NONE	FILENAME: 2079A_Rev1.PCB		SHT 1 of 1	