



REVISIONS			
REV	DESCRIPTION	APPR	DATE




NOTES : Unless Otherwise Specified

- 1. FAB PER IPC-A-600.
- 2. MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4. 2 OZ. COPPER THICKNESS .062 +/--.006 TOTAL OF 2 LAYERS. FLAMABILITY RATING: 94 V-0 MINIMUM .
- 3. DRILLING: DRILL HOLES PER SCHEDULE. PLATE THROUGH HOLES WITH COPPER, .001 INCH THICK MIN. ALL HOLE SIZES ARE SPECIFIED AFTER PLATING. HOLE LOCATION TOLERANCES ARE +/--.003 INCH IN RELATION TO CENTER
- 4. SOLDER MASK : SMOBC USING LPI BOTH SIDES COLOR GREEN.
- 5. FINISH: SMOBC USING LPI BOTH SIDES COLOR GREEN.
- 6. SILKSCREEN : USING WHITE NON-CONDUCTIVE EPOXY INK.
- 7. DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
- 8. SCORING:



FAB DRAWING

APPROVALS		 LINEAR TECHNOLOGY		1630 McCarthy Blvd. Milpitas, CA 95035 PH: (408)432-1900	
		INIT	DATE		
DRAWN					
CHECK					
DESIGN	JUNE WU	12/30/04			
ENGR	Kevin Huang	12/30/04			
TITLE:			LTC3410ESC6		
			2.25MHz High Efficiency Synchronous Step-Down Converter		
SIZE		A	DEMO	DC870A	REV. A
SCALE = NONE			DES:230737		
			SHT 1 of 1		

SIZE	QTY	SYM	PLTD
15	4	+	PLTD
95	6	X	PLTD
35	3	#	PLTD
70	2	◇	NPLTD