


SIZE	QTY	SYM	PLTD
95	7	+	PLTD
35	9	×	PLTD
125	4	□	PLTD
15	91	◇	PLTD

NOTES : Unless Otherwise Specified


- 1. FAB PER IPC-A-600.
- 2. MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4, 2 OZ. COPPER THICKNESS .062 +/- .006 TOTAL OF 4 LAYERS. FLAMABILITY RATING: 94 V-0 MINIMUM .
- 3. DRILLING: DRILL HOLES PER SCHEDULE. PLATE THROUGH HOLES WITH COPPER, .001 INCH THICK MIN. ALL HOLE SIZES ARE SPECIFIED AFTER PLATING. HOLE LOCATION TOLERANCES ARE +/- .003 INCH IN RELATION TO CENTER
- 4. SOLDER MASK : SMOBC USING LPI BOTH SIDES COLOR GREEN.
- 5. SILKSCREEN : USING WHITE NON-CONDUCTIVE EPOXY INK.
- 6. DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.



FAB DRAWING

APPROVALS

DRAWN	INIT	DATE
CHECK		
DESIGN	JUNE WU	4/6/01
ENGR		

 **LINEAR TECHNOLOGY**

1630 McCarthy Blvd.
Milpitas, CA 95035
PH: (408)432-1900

TITLE: LTC3713, Low Input Voltage,
High Current Buck Controller

SIZE A DEMO DC412A REV. A

SCALE = NONE

DES-230440

SHT 1 of 1