



REVISION HISTORY

ECO	REV	DESCRIPTION	DATE	APPROVED
	2	PROTO	03/11/05	




TOP COMPONENT SIDE SHOWN



NOTES: UNLESS OTHERWISE SPECIFIED.

- ARTWORK P/N DC884A REV 2.
- FAB PER IPC-A-600
- MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4, .005 INCH THICKNESS, INTERLAYER AND CORE LAYERS, 2 OZ COPPER ON FOUR INTERNAL LAYERS, FLAMABILITY RATING: 94 V-2 MINIMUM
- SIZE: CUT TO DIMENSIONS AND TOLERANCES SHOWN. 0.00 ARE PRIMARY DATUMS
- BOARD: SELECTIVE PLATED BOARD, SOLDER MASK OVER BARE COPPER, COLOR: GREEN LPL, WHITE TIN IMERSION (QUICKSILVER) BOTH SIDES, NON-CONDUCTIVE INK
- DRILL: ALL HOLES SHALL BE DRILLED $\pm .003$ INCH WITH RESPECT TO CTR. OF DRILLED PAD. ALL HOLES FINISHED SIZE AFTER PLATING.
- DROP ALL UNUSED PADS ON INNER LAYERS.
- DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
- SCORING:



SIZE	QTY	SYM	PLTD	TOL
10	68	+	YES	$\pm .0003$
20	66	X	YES	$\pm .0003$
35	15	□	YES	$\pm .0003$
65	11	◇	YES	$\pm .0005$
70	2	⊗	NO	$\pm .0005$
187	4	⊕	NO	$\pm .001$
205	6	⊕	YES	$\pm .001$

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON ANGLE $\pm P$ 2 PLACE $\pm .01$ 3 PLACE $\pm .005$ INTERPRET DIM AND TOL PER ASME Y14.5M - 1994 THIRD ANGLE PROJECTION	CONTRACT NO		APPROVALS		DATE
	DRAWN		MEI		01/31/05
	CHECKED				
	APPROVED		ENGINEER		
DO NOT SCALE DRAWING					
SCALE 1/1					
FILENAME: 884A-2.PCB					
SHEET 1 OF 1					

LTC TECHNOLOGY		1630 McCarthy Blvd. Milpitas, CA 95035 Phone: (408)432-1900 Fax: (408)434-0507	
TITLE			
FAB, LTC3828EUH, DUAL OUTPUT HIGH DENSITY 17A STEP DOWN DC/DC WITH TRACKING			
SIZE	CAGE CODE	DWG NO	REV
B		DC884A	2
SCALE 1/1			
FILENAME: 884A-2.PCB			
SHEET 1 OF 1			