



# NOTES : Unless Otherwise Specified

1. FAB PER IPC-A-600.
2. MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4, 2 OZ. COPPER  
THICKNESS .062 +/- .006 TOTAL OF 2 LAYERS.  
FLAMABILITY RATING: 94 V-0 MINIMUM .
3. DRILLING: DRILL HOLES PER SCHEDULE. PLATE THROUGH  
HOLES WITH COPPER, .001 INCH THICK MIN. ALL  
HOLE SIZES ARE SPECIFIED AFTER PLATING.  
HOLE LOCATION TOLERANCES ARE +/- .003  
INCH IN RELATION TO CENTER
4. SOLDER MASK : SMOBC USING LPI BOTH SIDES COLOR GREEN.
5. SILKSCREEN : USING WHITE NON-CONDUCTIVE EPOXY INK.
6. DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.

7. SCORING:



SIZE	QTY	SYM	PLTD
95	20	+	PLTD
35	38	X	PLTD
55	59	□	PLTD
40	68	◇	PLTD
15	56	⊗	PLTD
70	2	⊗	NPLTD
45	20	A	PLTD
187	5	B	PLTD

FAB DRAWING

<b>APPROVALS</b> DRAWN _____ CHECK _____ DESIGN JUNE WU 5/23/01 ENGR _____		1630 McCortly Blvd. Milpitas, CA 95035 PH: (408)432-1900 <b>LINEAR TECHNOLOGY</b>	
TITLE: LTC1966CMS8 RMS to DC Converter			
SIZE	DEMO	REV.	B
SCALE = NONE		DES-240003	
		SHT 1 of 1	