


SIZE	QTY	SYM	PLTD
15	44	+	PLTD
95	8	X	PLTD
35	14	□	PLTD
70	2	◇	NPLTD

NOTES : Unless Otherwise Specified

1. FAB PER IPC-A-600.
2. MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4. 2 OZ. COPPER THICKNESS .062 +/- .006 TOTAL OF 4 LAYERS. FLAMABILITY RATING: 94 V-0 MINIMUM .
3. DRILLING: DRILL HOLES PER SCHEDULE. PLATE THROUGH HOLES WITH COPPER, .001 INCH THICK MIN. ALL HOLE SIZES ARE SPECIFIED AFTER PLATING. HOLE LOCATION TOLERANCES ARE +/- .003 INCH IN RELATION TO CENTER
4. SOLDER MASK : SMOBC USING LPI BOTH SIDES COLOR GREEN.
5. SILKSCREEN : USING WHITE NON-CONDUCTIVE EPOXY INK.
6. DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
7. LAYER 2 AND LAYER 3 ARE IDENTICAL.
8. SCORING:



9. There are two silkscreen top on this order. 400 pcs for DC432A and 200 pcs for DC432B.

FAB DRAWING

APPROVALS		LINEAR TECHNOLOGY		1630 McCarthy Blvd. Milpitas, CA 95035 PH: (408)432-1900	
DRAWN	INIT	DATE			
CHECK					
DESIGN	JUNE WU	5/24/01	TITLE: LTC1879EGN/LTC1875EGN, High Efficiency Synchronous Step-Down Regulator		
ENGR	TOM G.	5/24/01			
			SIZE	A	REV. A
			DC432A / DC432B		
SCALE = NONE			SHT 1 of 1		