



REVISION HISTORY

ECO	REV	DESCRIPTION	DATE	APPROVED




LAYER CONSTRUCTION

COMPONENT SIDE SHOWN

NOTES: UNLESS OTHERWISE SPECIFIED:

- ARTWORK P/N DC886A Rev 2.
- FAB PER IPC-A-600
- MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4 .062 +/- .005 INCH THICKNESS WITH 2 OZ. COPPER FINISH ON TWO OUTER LAYERS AND 1 OZ. COPPER ON TWO INTERNAL LAYERS. FLAMABILITY RATING: 94 V-2 MINIMUM .
- SIZE: CUT TO DIMENSIONS AND TOLERANCES SHOWN. 0.00 ARE PRIMARY DATUMS.
- BOARD: SELECTIVE PLATED BOARD. SOLDER MASK OVER BARE COPPER, COLOR, GREEN LPI. WHITE TIN IMMERSION (OMIKRON) BOTH SIDES. SILKSCREEN COMPONENT SIDE WITH WHITE NON-CONDUCTIVE INK. PLATE THRU ALL HOLES WITH COPPER MIN. PLATING THICKNESS: 1 OZ. EXCEPT WHERE PLATING NOT REQUIRED
- DRILL: ALL HOLES SHALL BE DRILLED +/- .003 INCH WITH RESPECT TO CTR. OF DRILLED PAD. ALL HOLES FINISHED SIZE AFTER PLATING.
- DROP ALL UNUSED PADS ON INNER LAYERS.
- DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
- SCORING:



SIZE	QTY	SYM	PLTD	TOL
10	4	+	YES	+/-0.003
35	9	X	YES	+/-0.003
70	2	□	NO	+/-0.005
94	5	◇	YES	+/-0.005

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON ANGLE ± 1° 2 PLACE ± .01 3 PLACE ± .005 INTERPRET DIM AND TOL PER ASME Y14.5M - 1994	CONTRACT NO.		1630 McCarthy Blvd. Milpitas, CA 95035 Phone: (408)432-1900 Fax: (408)434-0507	
	APPROVALS	DATE	TITLE	
	DRAWN MEI	01/14/05	FAB, LTC3035EDDB, VLDO LINEAR REGULATOR	
	CHECKED APPROVED		SIZE A	CAGE CODE DC886A
DO NOT SCALE DRAWING	DESIGNED BY	SCALE 1/1	FILENAME: 886A-2.PCB	SHEET 1 OF 1