


- ART01 = LAYER 1 (COMPONENT SIDE)
- ART02 = LAYER 2 (GND)
- ART03 = LAYER 3 (SIGNAL)
- ART04 = LAYER 4 (SOLDER SIDE)

NOTES : Unless Otherwise Specified

1. MATERIAL : FR4 OR EQUIVALENT EPOXY, 2 OZ. COPPER CLAD
THICKNESS .062 +/- .006 TOTAL OF 4 LAYERS
2. FINISH : ALL PLATED HOLES .001 MIN. / .0015 MAX. COPPER PLATE
WHITE TIN IMMERSION (OMIKRON) BOTH SIDES.
BEFORE REFLOW , SOLDER MASK OVER BARE COPPER (SNOBC)
3. SOLDER MASK : BOTH SIDES USING GREEN LPI
4. SILKSCREEN : USING WHITE NON-CONDUCTIVE EPOXY INK
5. ALL DIMENSIONS ARE IN INCHES
6. SCORING: NOT REQUIRED FOR PROTOTYPE



Fabrication Drawing

SIZE	QTY	SYM	PLTD	TOL
95	7	+	YES	+/-0.0
40	3	X	YES	+/-0.0
70	2	□	NO	+/-0.0
15	14	◇	YES	+/-0.0

APPROVALS		LINEAR TECHNOLOGY		1630 McCarthy Blvd. Milpitas, CA 95035 PH: (408)432-1900	
DRAWN	INIT	DATE			
CHECK					
DESIGN					
ENGR					
TITLE: LT3487EDD					
Boost and Inverting DC/DC Converters					
SIZE	A	DC912A	REV.	A	
SCALE = NONE			DES-		
			SHT 1 of 1		