


SIZE	QTY	SYM	PLTD
95	7	+	PLTD
35	14	X	PLTD
15	53	□	PLTD
70	2	◇	NPLTD

# NOTES : Unless Otherwise Specified

- FAB PER IPC-A-600.
- MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4, 2 OZ. COPPER THICKNESS .062 +/- .006 TOTAL OF 4 LAYERS. FLAMABILITY RATING: 94 V-0 MINIMUM .
- DRILLING: DRILL HOLES PER SCHEDULE. PLATE THROUGH HOLES WITH COPPER, .001 INCH THICK MIN. ALL HOLE SIZES ARE SPECIFIED AFTER PLATING. HOLE LOCATION TOLERANCES ARE +/- .003 INCH IN RELATION TO CENTER
- SOLDER MASK : SMOBC USING LPI BOTH SIDES COLOR GREEN.
- SILKSCREEN : USING WHITE NON-CONDUCTIVE EPOXY INK.
- DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
- LAYER 2 AND LAYER 3 ARE IDENTICAL.
- SCORING:



## FAB DRAWING

<b>APPROVALS</b>		<b>LINEAR TECHNOLOGY</b>		1630 McCarthy Blvd. Milpitas, CA 95035 PH: (408)432-1900	
DRAWN	INIT	DATE			
CHECK					
DESIGN	JUNE WU	7/11/01	TITLE: LTC3411 Buck Regulator		
ENGR	TOM G.	7/11/01	2.65V-5.5V->1.8V, 2.5V, or 3.3V@1.25A(max)		
			SIZE	DEMO	DC441A
					REV. A
SCALE = NONE			DES-230463		SHT 1 of 1