



REVISIONS			
REV	DESCRIPTION	APPR	DATE
A	PROTOTYPE RELEASE		

NOTES : Unless Otherwise Specified


1. FAB PER IPC-A-600.
2. MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4, 2 OZ. COPPER THICKNESS .062 +/- .006 TOTAL OF 4 LAYERS.
FLAMABILITY RATING: 94 V-0 MINIMUM .
3. DRILLING: DRILL HOLES PER SCHEDULE. PLATE THROUGH HOLES WITH COPPER, .001 INCH THICK MIN. ALL HOLE SIZES ARE SPECIFIED AFTER PLATING.
HOLE LOCATION TOLERANCES ARE +/- .003 INCH IN RELATION TO CENTER
4. SOLDER MASK : SMOBC USING LPI BOTH SIDES COLOR GREEN.
5. SILKSCREEN : USING WHITE NON-CONDUCTIVE EPOXY INK.
6. DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
7. LAYER 2 AND LAYER 3 ARE IDENTICAL.

8. SCORING:



SIZE	QTY	SYM	PLTD
95	5	+	PLTD
35	6	X	PLTD
15	20	□	PLTD
70	2	⊗	NPLTD

FAB DRAWING

<div>APPROVALS</div>					<div>LINEAR TECHNOLOGY</div>		1630 McCarthy Blvd. Milpitas, CA 95035 PH: (408)432-1900		TITLE: LTC1733EMS Li-Ion Battery Charger	
DRAWN			INIT		DATE					
CHECK										
DESIGN			JUNE WU		8/29/01					
ENGR			FRAN H.		8/29/01					
							SIZE		REV.	
							A		A	
							DEMO		LTC1733EMSE	
							DC454A			
									SHT 1 of 1	