


LTC CONFIDENTIAL - For Customer Use Only

REVISION HISTORY


ECO	REV	DESCRIPTION	DATE	APPROVED
	2	PROD	06/16/05	

NOTES: UNLESS OTHERWISE SPECIFIED,

- ARTWORK P/N DC915A REV 2.
- FAB PER IPC-A-600
- MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4 .062 +/- .005 INCH THICKNESS WITH 2 OZ. COPPER FINISH ON TWO OUTER LAYERS AND 1 OZ. COPPER ON TWO INTERNAL LAYERS. FLAMABILITY RATING: 94 V-2 MINIMUM .
- SIZE: CUT TO DIMENSIONS AND TOLERANCES SHOWN. 0.00 ARE PRIMARY DATUMS.
- BOARD: SELECTIVE PLATED BOARD. SOLDER MASK OVER BARE COPPER, COLOR, GREEN LPI. WHITE TIN IMMERSION (OMIKRON) BOTH SIDES. SILKSCREEN COMPONENT SIDE WITH WHITE NON-CONDUCTIVE INK.  
PLATE THRU ALL HOLES WITH COPPER  
MIN. PLATING THICKNESS: 1 OZ. EXCEPT WHERE PLATING NOT REQUIRED
- DRILL: ALL HOLES SHALL BE DRILLED +/- .003 INCH WITH RESPECT TO CTR. OF DRILLED PAD.  
ALL HOLES FINISHED SIZE AFTER PLATING.
- DROP ALL UNUSED PADS ON INNER LAYERS.
- DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.



SIZE	QTY	SYM	PLTD	TOL
10	17	+	YES	+/-0.003
35	9	X	YES	+/-0.003
70	2	□	NO	+/-0.005
95	10	◇	YES	+/-0.01



<b>LINEAR TECHNOLOGY</b> 1630 McCarthy Blvd. Milpitas, CA 95035 Phone: (408)432-1900 Fax: (408)434-0507	CONTRACT NO.		TITLE	
	APPROVALS		DATE	
	DRAWN	MEI	04/05/05	
	CHECKED			
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON ANGLE ± 1° 2 PLACE ± .01 3 PLACE ± .005 INTERPRET DIM AND TOL PER ASME Y14.5M - 1994	THIRD ANGLE PROJECTION		FAB, LT3466EDD-1, WLED DRIVER AND LCD BIAS	
	DO NOT SCALE DRAWING		SIZE	REV
			A	2
			CAGE CODE	DWG NO.
		SCALE	1/1	FILENAME: 915A-2.PCB
		SHEET	1	OF 1