


SIZE	QTY	SYM	PLTD
95	5	+	PLTD
35	3	×	PLTD
15	8	□	PLTD
70	2	⊗	NPLTD

NOTES : Unless Otherwise Specified

1. FAB PER IPC-A-600.
2. MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4, 2 OZ. COPPER THICKNESS .062 +/--.006 TOTAL OF 2 LAYERS. FLAMABILITY RATING: 94 V-0 MINIMUM .
3. DRILLING: DRILL HOLES PER SCHEDULE. PLATE THROUGH HOLES WITH COPPER, .001 INCH THICK MIN. ALL HOLE SIZES ARE SPECIFIED AFTER PLATING. HOLE LOCATION TOLERANCES ARE +/--.003 INCH IN RELATION TO CENTER
4. SOLDER MASK : SMOBC USING LPI BOTH SIDES COLOR GREEN.
5. SILKSCREEN : USING WHITE NON-CONDUCTIVE EPOXY INK.
6. DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
7. SCORING:



FAB DRAWING

APPROVALS		INIT		DATE	
DRAWN					
CHECK					
DESIGN		JUNE WU		1/9/02	
ENGR		B. Walter		8/2/00	
TITLE:		LTC3250ES6-1.5 High Efficiency, Low Noise, Inductorless Step Down DC/DC Converter			
SIZE		A		REV. A	
SCALE = NONE		DES-230512		SHT 1 of 1	

1630 McCarthy Blvd.
Milpitas, CA 95035
PH: (408)432-1900