



Linear Tech. Corp.
Demo Circuit 526 RevA



NOTES: Unless Otherwise Specified

1. MATERIAL: 4 LAYERS, 0.062" THK. FR-4 GLASS EPOXY 1 OZ. COPPER CLAD.
2. ALL HOLE SHALL BE PLATED THRU.
3. PLATE THRU HOLES WITH COPPER .0014 MIN. THICKNESS. ALL HOLE SIZES IN HOLE TABLE ARE AFTER PLATING.
4. SILKSCREEN: WITH WHITE EPOXY NON-CONDUCTIVE INK.
5. NO SILKSCREEN ALLOWED ON PADS LANDS.
6. SOLDER MASK: LPI, GREEN.
7. NO BLOCK SOLDERMASKING OF PADS ROWS.
8. DO NOT MAKE CHANGES ON SILKSCREEN, SUCH AS COMPANY LOGO, QC STAMPS.
9. DO NOT PLATE TOOLING(3PLCS) AND SCORING(26PLCS) HOLES. (Reference Drawing Dwg No. DC205A)
10. SCORING:



| SIZE | QTY | SYM | PLTD |
|------|-----|-----|-------|
| 10 | 23 | + | PLTD |
| 31 | 6 | □ | PLTD |
| 94 | 9 | ◇ | PLTD |
| 63 | 2 | ⊠ | PLTD |
| 125 | 4 | B | PLTD |
| 63 | 2 | C | NPLTD |

Fabrication Drawing

| | | | | | |
|--------------|----------|-------------------|---|--|--------|
| APPROVALS | | LINEAR TECHNOLOGY | | 1630 McCarthy Blvd. Milpitas, CA 95035 PH: (408)432-1900 | |
| DRAWN | INIT | DATE | | | |
| CHECK | | | | | |
| DESIGN | RmB | | TITLE: LT1310EMSE | | |
| ENGR | JShannon | | Boost DC/DC Converter w/Phase-Locked Loop | | |
| | | | SIZE | Demo Circuit 526 | REV. A |
| | | | NONE | | |
| SCALE = NONE | | | DES-230549 | | |
| | | | SHT 1 of 1 | | |