



REVISIONS			
REV	DESCRIPTION	APPR	DATE




SIZE	QTY	SYM	PLTD
95	8	+	PLTD
120	2	X	PLTD
100	1	□	PLTD
35	9	◇	PLTD
125	4	⊗	PLTD
70	2	⊗	NPLTD
15	77	A	PLTD

NOTES : Unless Otherwise Specified

1. FAB PER IPC-A-600.
2. MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4.
.062 +/- .005 INCH THICKNESS WITH 2 OZ.
COPPER FINISHED ON 4 LAYERS.
FLAMABILITY RATING: 94 V-0 MINIMUM .
3. DRILLING: DRILL HOLES PER SCHEDULE: PLATE THROUGH HOLES WITH COPPER, .001 INCH THICK MIN. ALL HOLE SIZES ARE SPECIFIED AFTER PLATING.
HOLE LOCATION TOLERANCES ARE +/- .003 INCH IN RELATION TO CENTER
4. SOLDER MASK : SMOBC USING LPI BOTH SIDES COLOR GREEN.
5. SILKSCREEN : USING WHITE NON-CONDUCTIVE EPOXY INK.
6. DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
7. L2 AND L3 ARE IDENTICAL.



FAB DRAWING

APPROVALS		 LINEAR TECHNOLOGY		1630 McCarthy Blvd. Milpitas, CA 95035 PH: (408)432-1900	
DRAWN	INIT	DATE			
CHECK					
DESIGN	June W.	5/59/02	TITLE:		
ENGR	John S.	5/29/02	LTC1980EGN, Regulator/Battery Charger Controller		
			SIZE	A	REV. A
			DEMO	DC532A	
SCALE = NONE			DES-230		SHT 1 of 1