



REVISIONS			
REV	DESCRIPTION	APPR	DATE

NOTES : Unless Otherwise Specified

1. FAB PER IPC-A-600.
2. MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4.
2 OZ. COPPER FINISH ON OUTER LAYERS.
1 OZ. COPPER FINISH ON INNER LAYERS.
THICKNESS .062 +/- .006 TOTAL OF 4 LAYERS.
FLAMABILITY RATING: 94 V-0 MINIMUM .
3. SIZE: DIMENSIONS AND TOLERANCES SHOWN.
0.00 ARE PRIMARY DATUMS.
4. DRILLING: DRILL HOLES PER SCHEDULE. PLATE THROUGH HOLES WITH COPPER. .001 INCH THICK MIN. ALL HOLE SIZES ARE SPECIFIED AFTER PLATING.
5. FINISH: SMOBC USING LPI BOTH SIDES COLOR GREEN.
INCH IN RELATION TO CENTER

WHITE TIN IMMERSION (OMIKRON) BOTH SIDES.

6. SILKSCREEN : USING WHITE NON-CONDUCTIVE EPOXY INK.
7. DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
8. SCORING:(FOR PRODUCTION BOARDS)




SIZE	QTY	SYM	PLTD
95	13	+	PLTD
70	2	X	NPLTD
10	67	□	PLTD
8	8	◇	PLTD
65	3	⊗	PLTD

FAB DRAWING

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCES ON ANGLE ±1
2 PLACE ±.01 3 PLACE ±.005
INTERPRET DIM AND TOL
PER ASME Y14.5M - 1994

APPROVALS		INIT		DATE	
DRAWN					
CHECK					
DESIGN	JUNE WU			12/5/05	
ENGR	Keith S.			12/5/05	

SCALE = NONE		DES:		SHT 1 of 1	
--------------	--	------	--	------------	--



LINEAR
TECHNOLOGY

1630 McCarthy Blvd.
Milpitas, CA 95035
PH: (408)432-1900

TITLE:		LT3478EFE-1/LT3478EFE	
4.5A Boost LED Driver with PWM			

SIZE	A	DEMO	DC949A	REV.	A
------	---	------	--------	------	---