



Linear Tech. Corp.
Demo Circuit 567 RevA



NOTES: Unless Otherwise Specified

1. MATERIAL: 4 LAYERS, 0.062" THK. FR-4 GLASS EPOXY 1 OZ. COPPER CLAD.
2. ALL HOLE SHALL BE PLATED THRU.
3. PLATE THRU HOLES WITH COPPER .0014 MIN. THICKNESS. ALL HOLE SIZES IN HOLE TABLE ARE AFTER PLATING.
4. SILKSCREEN: WITH WHITE EPOXY NON-CONDUCTIVE INK.
5. NO SILKSCREEN ALLOWED ON PADS LANDS.
6. SOLDER MASK: LPI, GREEN.
7. NO BLOCK SOLDERMASKING OF PADS ROWS.
8. DO NOT MAKE CHANGES ON SILKSCREEN, SUCH AS COMPANY LOGO, QC STAMPS.
9. DO NOT PLATE TOOLING(3PLCS) AND SCORING(26PLCS) HOLES. (Reference Drawing Dwg No. DC205A)
10. SCORING:



SIZE	QTY	SYM	PLTD
125	4	+	PLTD
94	13	×	PLTD
10	22	□	PLTD
31	6	◇	PLTD
70	2	⊗	NPLTD

Fabrication Drawing

APPROVALS		LINEAR TECHNOLOGY		1630 McCarthy Blvd. Milpitas, CA 95035 PH: (408)432-1900	
DRAWN	INIT	DATE			
CHECK					
DESIGN	RmB				
ENGR	JShannon				
SCALE = NONE			SIZE NONE		REV. A
			Demo Circuit 567		
			DES-230589		SHT 1 of 1

TITLE: LTC4053EMSE-4.2/LTC4410ES6
USB Compliant Battery Charger